

PHILIPS

Steam iron

Azur

55 g/min continuous steam

250g steam boost

SteamGlide Elite soleplate



GC4909/60



Perfect results, every time

With our best scratch resistant soleplate

Long lasting performance with Quick Calc Release and SteamGlide Elite soleplate with enhanced scratch resistance.

Faster ironing and powerful performance

- Up to 250 g steam boost blasts stubborn creases
- 3000W for quick heat-up and powerful performance
- Steam output up to 55g/min for faster crease removal

Comfortable ironing

- Quick calc release system for an easy cleaning of your iron
- Automatic shut-off when the iron is left unattended

Easy ironing

- Drip-stop system keeps garments spotless while ironing
- Less refilling with extra-large 300 ml water tank

Easy gliding on all fabrics

- SteamGlide Elite: Our best gliding and scratch resistance

Highlights

Steam boost up to 250 g



Penetrates deeper into fabrics to easily remove stubborn creases.

3000W to heat up quickly



Delivers a fast warm-up and powerful performance to get your ironing done quickly

Continuous steam up to 55g/min




Strong and consistent steam output penetrates up to 50% more steam through fabric to remove creases faster.

Quick Calc Release



Quick Calc Release for an easy cleaning of your iron and a long-lasting steam performance

Auto shut-off



The iron shuts itself off if you leave it standing still. On its soleplate, it will automatically switch off after 30 seconds. On its heel rest, it will automatically switch off after 8 minutes.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank. So you can iron more clothes in one go.

SteamGlide Elite soleplate



Our exclusive SteamGlide Elite is our best soleplate for ultimate gliding and maximum scratch resistance.

Specifications

Technology

For all ironable fabrics

Fast crease removal

Continuous steam: 55 g/min

Power: 3000 W

Pressure: 55g/min

Ready to use: 2 min

Steam boost: 250 g

Variable steam levels

Vertical steam

Voltage: 240 V

Water spray

Easy to use

Soleplate gliding performance: 4 stars

Soleplate name: SteamGlide Elite

Water tank capacity: 300 ml

Cord freedom (swivel): 360 degree cord freedom

Drip Stop

Integrated power plug

Power cord length: 3 m

Select steam level from handle

Soleplate scratch resistance: 5 stars

Tap water suitable

Auto shut-off

Indicator light

Scale management

Descaling and cleaning: Quick Calc Release

Size and weight

Packaging dimensions (WxHxL): 13.7 x 16.7 x 33.2 cm

Product dimensions (WxHxL): 12.88 x 15.33 x

31.95 cm

Total weight with packaging: 1.908 kg

Weight of iron: 1.669 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Product packaging: 100% recycable

User manual: 100% recycled paper

