

PHILIPS

Steam iron

PerfectCare Azur

Steam 50g/min; 190g steam boost

Fabric shaver

Safety Auto off + Anti-calc

Safe for all ironable garments



GC4914/27



Carefree ironing, no setting required

Ironing perfected

Iron any ironable garment from silk, to linen, to cotton, to cashmere; in any order without adjusting the temperature. PerfectCare Azur delivers perfect results without the risk of burn or shine.

Comfortable ironing

- Iron with smart light feedback indicator
- Quattro Precision Tip for an easy reach in tricky areas
- T-ionicGlide: our best 5-star rated soleplate
- Iron switches off automatically when left unattended
- Fabric shaver for removing pills from all types of garment

One perfect setting for all your clothes

- 100% easy to use, no adjustment required
- 100% safe on all ironable garments
- 100% fast on all fabrics, no other steam iron is faster
- OptimalTemp technology: perfect combination of temperature

Fast and powerful ironing

- 2600 W iron for fast heat-up and powerful performance
- Steam output of up to 50 g/min for better crease removal
- Steam boost up to 190 g



asimpleswitch.com

Highlights

OptimalTemp technology



The latest revolution in ironing to deliver the perfect combination of steam and temperature. It's made to ensure you with speedy ironing, great results on tough creases, no setting required and safe on all ironable fabrics. The perfect combination of steam and temperature because: 1) Smart Control Processor setting the right temperature 2) HeatFlow technology enabling an even steam and temperature balance.

100% safe



100% safe on all fabrics even the most delicate like silk, cashmere, wool, polyester. Independent iron testing institutes have used PerfectCare on the most sensitive ironable garments and they confirmed the excellence of ironing results.

100% fast

100% fast to iron, no sorting required. Iron all your garments with more effective steam.

100% easy to use



100% easy to use, no adjustment required. You can now iron all ironable garments one after the other, without having to wait or to adjust the iron's temperature dial.

2600 W for fast heat-up



2600 W iron for fast heat-up and powerful performance on all your ironable garments.

Steam boost up to 190 g



The steam boost can be used for vertical steaming and tough creases.

Steam up to 50 g/min



Continuous steam output of up to 50 g/min gives you the perfect amount of steam to efficiently remove all creases.

Fabric Shaver



Easily removes fabric pills from all types of garments. All your garments, whether it is your sweater or your blanket, will look like new again.

T-ionicGlide soleplate



T-ionicGlide is Philips most premium soleplate. Delivering a new standard in glide and scratch resistance for OptimalTemp irons. The patented new coating will secure excellent results. The carefully designed shape and vent holes provide an even steam distribution for easy crease removal with the steam iron.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Fast & powerful crease removal

Soleplate: T-ionicGlide
OptimalTEMP technology
Continuous steam output: Up to 50 g/min
Steam boost: 190 g
Spray
Power: 2600 W

Easy to use

Water tank capacity: 350 ml
Drip stop
Safety auto off
Cord storage: Cord clip

Power cord length: 2.5 m
Cord freedom (swivel): 180 degree cord freedom
Fast and easy filling

Sustainability

Energy saving: 10% energy reduction

Calc management

Suitable for tap water
Calc clean solution: Double active calc clean

Technical specifications

Weight of iron: 1.75 kg

Accessories

Fabric shaver

Comfortable ironing

Cord length: 2.5 m

