

# PHILIPS

## Steam iron

### PerfectCare Azur

Steam 50 g/min; 210 g steam boost

T-ionicGlide soleplate

Safety Auto off + Anti-calc

Safe for all ironable garments



GC4928/30

## Fastest Philips steam iron\*

### From jeans to silk in one go

Iron any ironable garment from jeans to silk, from linen to cashmere safely in one go; in any order without temperature adjustment. PerfectCare Azur delivers perfect results with no risk of burn or shine. Ironing is now easier and faster.

#### One perfect setting for all your clothes

- OptimalTemp technology: perfect combination of temperature
- 100% safe on all ironable garments
- 100% fast on all fabrics; no other steam iron is faster
- 100% easy to use, no adjustment required
- Tested and approved by independent textile experts

#### Comfortable ironing

- T-ionicGlide: our best 5-star rated soleplate
- Suitable for tap water with Double Active Calc Clean system
- Iron switches off automatically when left unattended
- Innovative CordGuide

#### Fast and powerful ironing

- Steam output of up to 50 g/min for better crease removal
- 3000 W iron for fast heat-up
- Steam boost up to 210 g

# Highlights

## OptimalTemp technology



The latest revolution in ironing to deliver the perfect combination of steam and temperature. It's made to ensure you get speedy ironing and great results on tough creases, with no setting required, and is safe on all ironable fabrics. The perfect combination of steam and temperature because: 1) the Smart Control Processor sets the right temperature 2) the HeatFlow technology enables an even steam and temperature balance.

## 100% safe



100% safe on all fabrics even the most delicate like silk, cashmere, wool, polyester. Independent iron testing institutes have used PerfectCare on the most sensitive ironable garments and they confirmed excellent ironing results.

## 100% fast


100% fast to iron, no sorting required. Iron all your garments with more effective steam.

## 100% easy to use



100% easy to use, no adjustment required. You can now iron all ironable garments one after the other, without having to wait or to adjust the iron's temperature dial.

## Tested and approved:



This iron is tested and approved by independent textile expert institutes, such as DWI, IWTO and Woolmark, for its excellent ironing performance. The Woolmark Apparel Care programme helps consumers to identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips, with its exclusive OptimalTEMP technology, is so far the only brand to be certified with the Gold standard from Woolmark. You can be confident that Woolmark-approved apparel care products are ideal for any wool garments.

## T-ionicGlide soleplate



T-ionicGlide is Philips' premium soleplate. Delivering a new standard in glide and scratch-resistance for OptimalTemp irons. The patented new coating will secure excellent

results. The carefully designed shape and vent holes provide even steam distribution for easy crease removal with the steam iron.

## Suitable for tap water



PerfectCare Azur steam iron is designed to be used with tap water. Double Active Calc Clean: A smart combination of Calc Pills and a regular Self Clean reduce the scale built-up. For better ironing results we recommend to use demineralised water. This ensures a consistent steam flow from your iron.

## Safety auto off



The iron shuts off automatically when left unattended. If left on it's heelrest the steam iron will switch off in 3 minutes, when left resting on the soleplate it will take 2 minutes before the iron shuts off.

## CordGuide



The innovative CordGuide simply clicks onto your ironing board and guides the cord away while you iron.

# Specifications

## Fast and powerful crease removal

Soleplate: T-ionicGlide  
OptimalTEMP technology  
Continuous steam output: Up to 50 g/min  
Steam boost: 210 g  
Power: 3000 W  
Spray

## Comfortable ironing

Cord length: 2.5 m

## Easy to use

Water tank capacity: 350 ml  
Drip stop  
Soft grip

## Safety auto off

Cord storage: Cord clip  
Cord freedom (swivel): 180 degree cord freedom  
CordGuide: Keep your cord out of the way  
Fast and easy filling  
Power cord length: 2.5 m

## Sustainability

Energy saving: 10% energy reduction

## Calc management

Suitable for tap water  
Calc clean solution: Double active calc clean  
Calc clean reminder: Yellow flashing

## Technical specifications

Weight of iron: 1.75 kg

## Accessories

CordGuide  
Filling cup

