

PHILIPS

Steam Iron with
OptimalTEMP technology

Azur Advanced

3000 W

55 g/min continuous steam

230 g steam boost

SteamGlide Plus soleplate



GC4933/80



New generation iron for great results faster* Guaranteed no burns

Azur Advanced steam iron allows you to iron everything from jeans to silk with no risk of burning* thanks to OptimalTEMP technology. Steam output now penetrates up to 20% deeper into the fabric for faster crease removal.

Intelligent ironing for ultimate convenience

- OptimalTEMP technology: Guaranteed no burns, no settings

Easier and faster ironing

- 3000 W for quick heat-up and powerful performance
- Deep penetrating steam, for great results faster
- 55 g steam penetrates up to 20% more steam through fabric*
- Up to 230 g steam boost blasts stubborn creases

Comfortable ironing

- Smart calc reminder to remove calc from the iron
- Extra long cord for maximum reach
- SteamGlide Plus soleplate for ultimate easy gliding
- Automatic shut-off when the iron is left unattended



asimpleswitch.com

Highlights

OptimalTEMP technology



Thanks to OptimalTEMP technology, we guarantee this iron will never cause burns to any ironable fabric. Iron everything from jeans to silk, from linen to cashmere safely, in any order, without waiting for the temperature to adjust. Philips steam irons with OptimalTEMP make your ironing easier and faster and have been tested by independent textile experts.

3000 W for fast heat-up



Delivers a fast warm-up and powerful performance to get your ironing done quickly.

Extra long cord



An ultra-long 3-metre cord provides maximum reach and convenience.

Continuous steam up to 55 g/min



Strong and consistent steam output now penetrates up to 20% more steam through fabric to remove creases faster.

Steam boost up to 230 g




Penetrates deeper into fabrics to easily remove stubborn creases.

SteamGlide Plus soleplate



Our exclusive SteamGlide Plus soleplate – with its advanced titanium layer and 6-layer coating – delivers ultimate gliding performance over any fabric. Non-stick, scratch-resistant and easy to keep clean.

Smart calc-clean reminder




This iron has a smart calc-clean reminder which indicates when descaling is needed. Simply push the calc-clean button on the water tank to flush away the calc from the iron for long-lasting steam performance

Deep, penetrating steam

Thanks to the special design for maximum steam penetration, now up to 20%* more steam through the fabric for great results, faster.

Auto shut-off



The iron shuts itself off if you leave it standing still. On its soleplate, it will automatically switch off after 30 seconds. On its heel rest, it will automatically switch off after 8 minutes.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technology

OptimalTEMP technology

Fast crease removal

Continuous steam: 55 g/min

Power: 3000 W

Steam boost: 230 g

Vertical steam

Easy to use

Soleplate name: SteamGlide Plus

Water tank capacity: 330 ml

Extra-stable heel rest

Power cord length: 3 m

Drip-stop

Extra-large filling hole

Auto shut-off

Scale management

Descaling and cleaning: Self-clean

Size and weight

Product dimensions (W x H x D): 33.3 x 17.5 x 13.5 cm

Guarantee

2 year worldwide guarantee

Green efficiency

User manual: 100% recycled paper

