

PHILIPS

Steam Iron with
OptimalTEMP technology

Azur Elite

3000W

75 g/min continuous steam

260g steam boost

SteamGlide Advanced soleplate



GC5039/30



Our smartest and most powerful steam iron Guaranteed no burns, with intelligent steam release

Powerful, intelligent iron for perfect results faster. Iron everything from jeans to silk with no risk of burning thanks to OptimalTEMP technology. Advanced DynamiQ steam mode ensures the perfect amount of powerful steam when you need it*

Intelligent ironing for ultimate convenience

- OptimalTEMP technology: Guaranteed no burns, no settings
- DynamiQ mode, intelligent steam release for perfect results
- Convenient steam modes: DynamiQ, MAX, IONIC and OFF
- Ionic steam mode, deep ionized steam for hygienic ironing

Easier and faster ironing

- 3000 W for quick heat-up and powerful performance
- Turbo steam pump pushes up to 50% more steam through fabric*
- Steam output up to 75g/min for faster crease removal
- Up to 260 g steam boost blasts stubborn creases

Comfortable ironing

- SteamGlide Advanced soleplate, ultimate gliding & durability
- Smart calc reminder to remove calc from the iron
- Quick Calc Release in 15s for long-lasting steam performance
- Extra-long cord for maximum reach

Highlights

OptimalTEMP technology



Thanks to OptimalTEMP technology, we guarantee this iron will never cause burns to any ironable fabric and you can iron everything from jeans to silk, from linen to cashmere safely, in any order, without waiting for the temperature to adjust or pre-sorting clothes. Philips steam irons with OptimalTEMP makes your ironing easier and faster and has been tested by independent textile experts .

blasts stubborn creases with powerful continuous steam, IONIC steam mode with powerful steam bursts for more hygienic ironing and OFF steam enables you switch off the steam

Deep Ionic Steam



Ionic Steam mode produces deep and powerful ionic steam bursts for more hygienic ironing for your specific garment needs.

Extra-long cord



An ultra-long 3-meter cord provides maximum reach and convenience.

Turbo Steam power



Our built-in Turbo Steam pump delivers up to 50% more powerful continuous steam so creases disappear even quicker.

DynamiQ steam mode



Thanks to DynamiQ sensor, the most advanced motion sensor used in steam irons knows precisely how your iron is moving and when its standing still. DynamiQ steam mode releases automatically perfect amount of steam when its needed during your ironing to get the ironing results faster. The steam automatically starts when your iron is moving and stops when you don't move for ultimate convenience and effortless ironing.

3000 W for fast heat up



Delivers a fast warm-up and powerful performance to get your ironing done quickly

Continuous steam up to 75g/min



Strong and consistent steam output penetrates up to 50% more steam through fabric to remove creases faster.

Convenient steam modes



Choose from multiple steam modes. DynamiQ mode delivers the perfect amount of steam automatically when you need it, Max mode

SteamGlide Advanced soleplate



SteamGlide Advanced is our best soleplate for ultimate gliding performance and maximum scratch resistance. Its stainless steel base is twice as hard as a regular aluminum base, and our patented 6-layer coating with advanced titanium layer glides effortlessly for the fastest results.

Steam boost up to 260 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Specifications

Fast crease removal

Continuous steam: 75 g/min
Ionic Deep Steam
Power: 3000 W
Steam boost: 260 g
Vertical steam

Easy to use

Soleplate name: SteamGlide Advanced
Water tank capacity: 350 ml
Extra stable heel rest

Drip stop
Extra large filling hole
Auto shut-off

Comfortable ironing

Cord length: 3 m

Scale management

Descaling and cleaning: Quick Calc Release

Size and weight

Product dimensions (WxHxL): 33,3 x 17,5 x 13,5 cm

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
User manual: 100% recycled paper

