

PHILIPS

Pressurised steam
iron

PerfectCare Xpress

Steam 65g/min; 200g steam
boost

SteamGlide soleplate

Safety Auto off + Anti-calc

Safe for all ironable garments

GC5057/02



Carefree ironing, no setting required

With compact, powerful steam generator inside

Iron any ironable garment from silk, to linen, to cotton, to cashmere...in any order, without adjusting the temperature. Philips PerfectCare Xpress delivers great results without risk of burn or shine for all garments. Truly simple ironing

One perfect setting for all your clothes

- OptimalTemp: The perfect combination of steam and temperature
- 100% easy to use, no adjustment required
- 100% safe on all ironable garments
- 100% fast on all fabrics; no other steam iron is faster
- Tested and approved by independent textile experts

Fast and powerful ironing

- 2800 W iron for fast heat up and powerful performance
- Constant powerful steam up to 65 g/min
- Steam boost up to 200 g
- SteamGlide soleplate for powerful steam and superb gliding

Comfortable ironing

- 3 Safety Auto Off triggers
- Iron with smart light feedback indicator
- Auto Steam Sensor activates the steam automatically

Highlights

100% safe



100% safe on all fabrics even the most delicate like silk, cashmere, wool, polyester. Independent iron testing institutes have used PerfectCare on the most sensitive ironable garments and they confirmed excellent ironing results.

100% easy to use




100% easy to use, no adjustment required. You can now iron all ironable garments one after the other, without having to wait or to adjust the iron's temperature dial.

100% fast



100% fast to iron, no sorting required. Iron all your garments with more effective steam.

Tested and approved:



This iron is tested and approved by independent textile expert institutes, such as DWI, IWTO and Woolmark, for its excellent

ironing performance. The Woolmark Apparel Care programme helps consumers to identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips, with its exclusive OptimalTEMP technology, is so far the only brand to be certified with the Gold standard from Woolmark. You can be confident that Woolmark-approved apparel care products are ideal for any wool garments.

SteamGlide Soleplate




This specially designed soleplate combines superior ceramic coating for superior gliding on all fabrics and carefully designed vents for powerful crease removal.

2800 W for fast heat-up

2800 W max

2800 W iron for fast heat up and powerful performance on all your ironable garments.

Auto Steam Sensor



The innovative Auto Steam Sensor with motion detection activates the steam automatically when the iron is moved on the ironing board. This always gives you the right amount of

steam for effective crease removal, while reducing wasted steam. Great results and energy efficiency

Constant steam up to 65 g/min




Constant powerful steam up to 65 g/min for better crease removal for all your garments

Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

Smart light feedback



Smart light feedback indicates the status of the iron at any time.

Specifications

Fast and powerful crease removal

Soleplate: SteamGlide
OptimalTEMP technology
Continuous steam output: 65 g/min
Steam tip
Power: 2800 W
Vertical steaming
Steam boost: 200 g

Comfortable ironing

Cord length: 2.5 m

Easy to use
Water tank capacity: 320 ml
Drip stop
Soft grip
Safety auto off
Cord storage: Cord clip
Power cord length: 2.5 m

Cord freedom (swivel): 360 degree cord freedom

Safe for all fabrics: Even for delicates such as silks

Calc management

Suitable for tap water
Calc clean solution: Anti-calc tablets and rinsing

