

PHILIPS

Pressurised steam
iron

PerfectCare Xpress

Steam 65g/min; 200g steam
boost

SteamGlide soleplate

Safety Auto off + Anti-calc

Safe for all ironable garments

GC5060/00



Carefree ironing, no setting required

With compact, powerful steam generator inside

Iron any ironable garment from silk, to linen, to cotton, to cashmere...in any order, without adjusting the temperature. PerfectCare Xpress delivers great results without risk of burn or shine for all garments. Ironing is now trully simple

One perfect setting for all your clothes

- OptimalTemp: The perfect combination of steam & temperature
- 100% easy to use, no adjustment required
- 100% safe on all ironable garments
- 100% fast on all fabrics, no other steam iron is faster

Fast and powerful ironing

- 2800 W iron for fast heat up and powerful performance
- Constant powerful steam up to 65 g/min
- SteamGlide soleplate for powerful steam and superb gliding
- Steam boost up to 200 g

Comfortable ironing

- 3 ways of automatic shut-off
- Iron with smart light feedback indicator
- Auto Steam Sensor activates the steam automatically
- ECO setting for an efficient ironing

Highlights

100% safe



100% safe on all fabrics even the most delicate like silk, cashmere, wool, polyester. Independent iron testing institutes have used PerfectCare on the most sensitive ironable garments and they confirmed the excellence of ironing results.

100% easy to use



100% easy to use, no adjustment required. You can now iron all ironable garments one after the other, without having to wait or to adjust the iron's temperature dial.

100% fast

100% fast to iron, no sorting required. Iron all your garments with more effective steam.

SteamGlide Soleplate



This specially designed soleplate combines superior ceramic coating for superior gliding on all fabrics and carefully designed vents for powerful crease removal.

2800 W for fast heat up



2800 W iron for fast heat up and powerful performance on all your ironable garments.

Auto Steam Sensor

The innovative Auto Steam Sensor with motion detection activates the steam automatically when moving the iron on the ironing board. This always gives you the right amount of steam for effective crease removal, while reducing the wasted steam. Great results and energy efficiency

Constant steam up to 65 g/min

Constant powerful steam up to 65 g/min for better crease removal for all your garments

Steam boost up to 200 g



The steam boost can be used for vertical steaming and tough creases.

OptimalTemp



One perfect setting for all your clothes. Always the perfect combination of steam & temperature because: 1) Advanced Smart Control Processor sets the perfect combination of steam & temperature 2) The ultra powerful cyclonic steam chamber delivers powerful constant steam for all your fabrics

Automatic shut-off



Iron shuts off automatically when the iron is hold still for 30s on soleplate, 30s lying on a side or standing on its heel rest for 8 minutes.

ECO setting

The ECO setting ensures efficient ironing with low energy consumption, due to an optimal amount of steam being generated

Specifications

Fast & powerful crease removal

Soleplate: SteamGlide
OptimalTEMP technology
Continuous steam output: 65 g/min
Vertical steaming
Steam tip
Power: 2800 W
Steam boost: 200 g

Comfortable ironing

Cord length: 2.5 m

Easy to use

Water tank capacity: 320 ml
Drip stop
Soft grip
Safety auto off
Cord storage: Cord clip
Power cord length: 2.5 m
Cord freedom (swivel): 360 degree cord freedom
Safe for all fabrics: Even for delicates like silks

Sustainability

ECO setting: 20% energy reduction

Calc management

Suitable for tap water
Calc clean solution: Anti-calc tablets + rinsing

Accessories

Included in pack: IronCare

