

PHILIPS

Garment Steamer

ComfortTouch

StyleBoard

1800W

3 steam settings



GC552/46



Effortless de-wrinkling from top to bottom with FlexHead and extra-long StyleBoard

Our new ComfortTouch garment steamer removes wrinkles and refreshes fabrics. With powerful continuous steam and an extra-long StyleBoard, clothes will be wrinkle free from top to bottom in no time.

Reliable and safe

- Safe on all ironable fabrics, no burns guaranteed
- Easy Rinse descaling for years of effective use
- PVC free silicon steam hose

Refresh without washing or dry cleaning

- Continuous steam removes odors and kills 99.9%* of bacteria

Quick crease removal

- Extra-long StyleBoard for better results from top to bottom
- Powerful continuous steam for fast crease removal
- Fabric brush for deeper steam penetration on thick garments

More efficient with less effort

- 3 steam settings for different kinds of fabrics
- Hang&Lock keeps your hanger securely in place
- With FlexHead to easily reach the bottom of garments

Highlights

Powerful continuous steam



Powerful continuous steam for fast crease removal

Extra-long StyleBoard


An extra long StyleBoard provides reliable support during steaming. Simply press the fabric between the steam plate and board for easier steaming with crisp results from top to bottom.

Brush accessory



Use the brush accessory with thicker garments like coats for better steam penetration and a smoother finish.

99.9% bacteria-free*



Hot steam refreshes your clothes and kills up to 99.9% of bacteria*. Less frequent washing and dry cleaning saves time and money, and helps clothes last longer.

With handy FlexHead

Innovative FlexHead lets you steam the bottom of garments easily, with less bending and kneeling. The flexible steam plate ensures maximum contact with the fabric so less steam escapes for efficient results.

3 steam settings



Set your preferred steam setting for optimal results on different fabrics. Use low steam for thinner fabrics and a more powerful setting for thicker fabrics and coats.

Hang&Lock



Our unique Hang&Lock feature holds your clothes hanger in place for convenient steaming. It prevents the hanger from swinging or falling off.

Safe on all ironable fabrics



The steamer is safe to use on all ironable fabrics and garments. The steam plate can be safely pressed against any clothing with no risk of burning – a great solution for delicate fabrics, like silk.

Easy Rinse descaling



Prolong the lifetime of your appliance by using the Easy Rinse descaling function regularly.

PVC free silicon steam hose



The steam hose is made of silicon material which is the safe and healthy choice for use with steam. As the safety and health of your family is important, no PVC is used in the steam hose.

Specifications

Technology

FlexHead Technology

Fast crease removal

Continuous steam: up to 35 g/min

Power: 1800 W

Ready to use: <1 min

Variable steam: 3 levels

Voltage: 220 - 240 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk

Water tank capacity: 1800 ml

Detachable water tank

Hang&Lock

Hose length: 1.3 m

Power cord length: 1.6 m

Silicone steam hose

Board cover

Top layer: 100% Cotton

Scale management

Descaling and cleaning: Easy Rinse

Accessories included

Brush

Garment hanger

Glove for extra protection

Adjustable double pole

Size and weight

Packaging dimensions (WxHxL):

37x46x64.5 cm

Product dimensions (WxHxL): 33x173x37 cm

Guarantee

2 year worldwide guarantee

Design

Color: Soft Blossom

Support for ironing

StyleBoard

