

PHILIPS

Garment Steamer

ClearTouch Air

2000W, AirStretch Technology

Hang&lock

3 steam levels

SmartFlow steam plate



GC562/30



Revive your delicate clothes with steam With innovative AirStretch technology

New ClearTouch Air garment steamer gives you better ironing results in one go, thanks to the innovative AirStretch technology and powerful steam. The suction gently stretches your clothes for safe and easy crease removal.

Better ironing results

- AirStretch technology for better ironing results in one go
- Extra powerful steam
- SmartFlow heated steam plate for great results
- Pleats made easy with pleat making accessory

More efficiency, less effort

- Unique Hang&Lock for stability during steaming
- 3 steam levels including ECO mode
- Detachable, transparent water tank with hygienic water inlet
- Easy Rinse descaling function
- Glove for extra protection during steaming
- Safe to use on delicate fabrics, like silk

Refreshes clothes without washing or dry cleaning

- Steam kills up to 99.9% of bacteria*
- Removes cigarette, food and body odors

Highlights

AirStretch Technology



Achieve better ironing results faster, with air suction. This innovative AirStretch technology uses adjustable suction force to gently pull and stretch the garment while keeping it close for deeper steam penetration. This combination helps you to achieve great ironing results with only one hand.

SmartFlow steam plate



SmartFlow technology ensures great ironing results as the optimized steam flow heats up the steam plate. This keeps the steam plate at an optimal, safe temperature for all fabrics while effectively preventing wet spots. It features a coating that enables good gliding and corrosion resistance.

Hang&Lock



Unique Hang&Lock feature locks the garment hanger and enables stability for more convenient steaming - even with your own hanger.

3 steam levels




Set your preferred steam level for optimal results on different kinds of garments. The ECO mode lets you save energy without compromising on results.

Detachable water tank



1.2 L detachable water tank with special water inlet for extra hygiene.

Easy Rinse descaling function



Prolong the lifetime of your appliance by using the Easy Rinse descaling function regularly.

Pleats made easy



Pleats made easy with pleat making accessory.

Steam kills bacteria

Hot steam kills up to 99.9% of bacteria on clothes and helps delaying washing or dry cleaning*.

Extra powerful steam



Powerful steam is blown through the nozzles, enabling you to remove creases with only a few strokes.

Glove for extra protection



Included is a glove that protects your hand during steaming.

Removes unwanted odors

Powerful steam removes cigarette, food and body odors.

Safe on all garments



The steamer is safe to use on all fabrics. It is a great solution for delicate fabrics like silk.

Specifications

Easy to use

Power cord length: 1.6 m

Water tank capacity: 1200 ml

Hang&Lock

Detachable water tank

Refill any time during use

Safe on all ironable fabrics: Even delicates like silk

Soleplate name: SmartFlow steam plate, XL steam plate

Special water inlet: For extra hygiene

Tap water suitable

Accessories included

Glove for extra protection

Pleat maker

Fast crease removal

Continuous steam: 40 g/min

Power: 2000 W

Voltage: 240 V

Variable steam: 3 levels

Scale management

Descaling and cleaning: Easy Rinse

Size and weight

Packaging dimensions (WxHxL):

40x45x33.3 cm

Product dimensions (WxHxL): 33x172x33 cm

Total weight with packaging: 5.73 kg

Weight of iron: 3.81 kg

Technology

AirStrech Technology

