

PHILIPS

Garment Steamer

ProTouch

2000 W

3 steam levels

Double pole with Hang&Lock



GC612/36



Professional results for all garments With PureSteam technology

Thanks to the innovative PureSteam technology, the new ProTouch garment steamer ensures powerful steam performance to give you professional results for years to come!*

Professional results

- Penetrating powerful steam with up to 3 bar pump pressure
- Precision tips for challenging areas

More efficiency, less effort

- PureSteam technology ensures powerful steam over the years
- No descaling is needed, thanks to the PureSteam technology
- 3 steam levels for different kinds of fabric

Reliable and safe

- Safe to use on all garments
- PVC free silicon steam hose
- Automatically switches to standby mode for safety

Highlights

Penetrating powerful steam



The innovative PureSteam technology is fundamentally different from other steamers. With up to 3 bar pump pressure, it generates powerful steam which penetrates deep into the garments, enabling you to remove creases with only a few strokes.

Powerful steam over the years



Other steamers are easy to lose steam performance over time due to scale build-up, even if you clean it regularly. With the innovative PureSteam technology, the heater is automatically descaled while generating steam. This prevents scale from building up. It is so effective that the steam is powerful for years to come*.

No descaling needed



Steamers need to be descaled regularly to ensure steam performance. With our new PureSteam technology, the heater is automatically descaled while generating steam, so you don't need to worry about it.

3 steam levels



Set your preferred steam level for optimal results on different kinds of fabric.

Precision tips



The Precision tips of the steamer head enable you to reach the challenging areas, such as the collar, the shoulder, and the in-between buttons, giving you precise results.

Auto shut off



When the water runs out, the power light will start blinking to remind you. If the product hasn't been used for another 8 minutes, it will go to standby mode automatically, ensuring safety.

Safe to use on all garments



The steamer is safe to use on all fabrics. It is a great solution for delicate fabrics like silk and cashmere.

PVC free silicon steam hose



The steam hose is made of silicon material which is the safe and healthy choice for use with steam. As the safety and health of your family is important, no PVC is used in the steam hose.

Specifications

Technology

PureSteam Technology

Fast crease removal

Continuous steam: up to 40 g/min

Power: 2000 W

Pressure: Max 3 bar pump pressure

Ready to use: <1.5 min

Variable steam: 3 levels

Easy to use

Safe on all ironable fabrics: Even delicates like silk

Soleplate name: SmartFlow Plus steam plate

Water tank capacity: 2000 ml

Detachable water tank

Hang&Lock

Hose length: 1.3 m

Power cord length: 1.6 m

Refill any time during use

Safety auto off

Silicone steam hose

Tap water suitable

Scale management

Descaling and cleaning: Auto de-calc

Accessories included

Brush

Collar aid

Glove for extra protection

Pants hanger

