

PHILIPS

Pressurized ironing
system

GC6360



Simple, fast and effective

Double your ironing speed with pressurized steam

The 6360 is created to reduce the ironing time. A shot of steam up to 110 g/min and a steam pressure up to 4 bar that penetrates deep into the fibres delivers an exceptionally fast and professional result even on difficult fabrics.

Fast and powerful ironing

- Up to 4 bars of steam pressure for fast ironing
- 110 g steam boost to remove stubborn creases easily
- Continuous steam up to 95 g/min
- Vertical steam for crease removal in hanging fabrics

Full control

- Variable steam settings to suit every garment

Smooth gliding

- Careeza soleplate for exceptional gliding on all fabrics

Highlights

Up to 4 bars steam pressure



Double your ironing speed with pressurized steam. Pressurized steam penetrates deep into fabrics, making your ironing fast and easy, even on difficult fabrics.

Specifications

Comfortable ironing

Additional comfort: Steam trigger lock

Anti-scale management: Easy Rinse

Cord length: 1,9 m

Hose length: 1.7 m

Safe in use: Overheat safety stop

Suitable for tap water

Crease removal

Soleplate: Optimal vent pattern

Easy to use

Control: Steam ready light, Temperature ready light, Water tank empty light

Reaching tricky areas: Button groove

Technical specifications

Boiler wattage: 1250

Frequency: 50-60

Iron wattage: 800

Start-up time: 8

Voltage: 220 - 240

Weight and dimensions

Product dimensions: 276 x 332 x 412

Product weight: 6,06

Weight carry case: 0.71

