

# PHILIPS

Steam generator  
iron

SpeedCare

Max 4.5 bar pump pressure

steam boost up to 120 g

1.2 L fixed watertank

GC6608



## Ironing faster with 2 x more steam\*\*

Philips SpeedCare steam generator delivers more steam than a steam iron, it helps you speed up ironing. Enjoy more quality time of the reduced ironing time with your loved family by using Philips SpeedCare steam generator iron.

### Fast and powerful ironing

- Max 4.5 bar pump pressure
- Ready to use in 2 minutes with unlimited refill
- Non-stick soleplate coating
- Refill the watertank at any time, even during ironing
- Triple precision tip for optimal control and visibility
- Continuous steam up to 95 g/min

### Comfortable ironing

- 1.2 L water tank and refill anytime during ironing
- Compact size and light weight iron for easier storage

### Easy to use

- Intelligent calc clean reminder with sound & light
- Vertical steam for crease removal in hanging fabrics

# Highlights

## Refill the watertank any time



The separate watertank allows you to re-fill the watertank any time, even during ironing, without waiting.

## Steam ready in 2 minutes



Steam is ready to use in 2min and can be refilled at anytime during ironing.

## Smart Calc Clean



Smart Calc Clean is an integrated descaling and cleaning function to protect your appliance. To ensure an optimal steam performance, long lasting life and in order to prevent white flakes, your steam generator iron will remind you to perform the descaling process. For maximum convenience make sure to always use the Smart Calc Clean container provided with your appliance.

## Vertical steam



This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

## 1.2 L water tank



SpeedCare steam generator has 1.2 L water tank capacity to allow your iron more than 1 hour, it helps you reduce the frequency of refilling everytime for the big laundry loads. The technology will also allow you refill the water tank during ironing without cooling down the appliance for 2 hours waiting to reill.

## Triple precision tip




The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

## Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.

## Compact size and light weight



SpeedCare steam generator has a very compact size, with 40% more compact than a steam generator in the market. Due to this fact, it also gives you the benefits carrying your steam generator iron is not a heavy job to do. Even though you have a small ironing board, and always put your steam generator iron on the floor, now you can place easily on your ironing board; Now you can carry your steam generator iron very easily everywhere and any place at your home for storage.

## Continuous steam



The more steam, the faster the ironing. The unique technology used in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

# Specifications

## Fast & powerful crease removal

Soleplate: Non-stick

Vertical steaming

Pressure: Max 4.5 bar pump pressure

Power: 2400 W

Steam boost: 120 g

Continuous steam output: 95 g/min

## Easy to use

Water tank capacity: 1200 ml

Filling and emptying water: Extra large filling hole

Refill any time

Heat up time: 2 min

Hose storage: Hose storage compartment

Cord freedom (swivel): 180 degree cord freedom

Hose length: 1.6 m

Power cord length: 1.8 m

## Calc management

Suitable for tap water

Calc clean solution: Smart Calc Clean

Calc clean reminder

Filtered water recommended

## Technical specifications

Weight of iron: 1.1 kg

Weight of iron + base: 2.6 kg

Product dimensions: 19.8 x 21.7 x 34.6 cm

Packaging dimensions: 26.4 x 30.3 x 40.4 cm

