

PHILIPS

Steam generator
iron

SpeedCare

Max 4.5 bar pump pressure

140 g steam boost

Carry lock

1.2 L fixed watertank

GC6613/27



Faster and easier ironing**

with 2 times more steam** than a steam iron

Philips SpeedCare steam generator delivers more steam than a steam iron, it helps you speed up ironing. Enjoy more quality time of the reduced ironing time with your loved family by using Philips SpeedCare steam generator iron.

Fast and powerful ironing

- Max 4.5 bar pump pressure
- Continuous steam up to 100 g/min
- 1.2 L water tank and refill anytime during ironing
- Triple precision tip for optimal control and visibility
- Lock your iron securely to the base station
- Smart Calc clean system with sound&light Calc Clean reminder
- Ready to use in 2 minutes with unlimited refill
- Compact size and light weight for easy storage

Highlights

Steam ready in 2 minutes




Steam is ready to use in 2min and can be refilled at anytime during ironing.

1.2 L water tank

SpeedCare steam generator has 1.2 L water tank capacity to allow your iron more than 1 hour, it helps you reduce the frequency of refilling everytime for the big laundry loads. The technology will also allow you refill the water tank during ironing without cooling down the appliance for 2 hours waiting to reill.

Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

Compact size and light weight

Thanks to the revolutionary ProVelocity technology, we made your steam generator iron more compact than ever before. The compact steam generator fits easily on your ironing board making your ironing more convenient. In addition, your steam generator takes much less storage space.

Smart Calc Clean system



Smart Calc Clean system is an intergrated descaling and cleaning fuction to protect your steam generator iron. After each about 10 hour ironing, you will be reminded by the soud and light of your steam genreator iron to perform calc clean process. The Calc Clean Container will provide you the convenience during the Calc Clean process, by just resting your iron on the container without holding your iron to stress your waist. After cleaning process, all the dirty water is collected in the container, your steam generator iron is ready to use again.

Max 4.5 bar pump pressure

The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

Safety carry lock



Your steam generator iron comes with a safety carry lock. You can lock your iron safely on the base, making it safer, reducing the risk of people touching the hot soleplate. You can also carry the steam generator easily.

Continuous steam

The more steam, the faster the ironing. The unique technology used in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

Specifications

Accessories included

Fabric Shaver

Easy to use

Hose length: 1.6 m

Power cord length: 1.8 m

Precision steam tip

Ready to use: Light indicator, Sound indicator

Refill any time during use

Soleplate gliding performance: 3 stars

Soleplate name: SteamGlide Ceramic

Soleplate scratch resistance: 3 stars

Tap water suitable

Water tank capacity: 1200 ml

Fast crease removal

Continuous steam: up to 100 g/min

Power: 2400 W

Pressure: Max 4.5 bar pump

Ready to use: 2 min

Steam boost: up to 140 g

Guarantee

2 year worldwide guarantee

Scale management

Descaling and cleaning: Smart Calc Clean

Descaling reminder: Light, Sound, Yes

Storage

Carry lock: For transportation and safety

Cord storage: Velcro fix

Hose storage: Hose storage compartment

Technology

ProVelocity steam engine

