

PHILIPS

Steam generator
iron

SpeedCare

Max 5 bar pump pressure

Up to 180 g steam boost

1.2 L water tank capacity

Compact design

GC6640



Faster and easier ironing

with 2 x more steam *

Philips SpeedCare steam generator delivers more steam than a steam iron, it helps you speed up ironing. Enjoy more quality time of the reduced ironing time with your loved family by using Philips SpeedCare steam generator iron.

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- Integrated easy clean system for long-lasting performance
- Great scratch resistance and easy gliding

Compact technology

- Lightweight and compact size for easy storage
- Optimized water tank for fast refilling
- Safe and secure carry lock
- Automatic switch off for safety and energy saving

Highlights

1.2 L water tank



The water tank has a large filling hole so you can easily fill it under the tap or alternatively with a jug or bottle at any time during ironing. It has a 1.2 L capacity, so you get the convenience of more than 1 hour of continuous use, with no need to top-up the tank.

Lightweight and compact size




Thanks to revolutionary ProVelocity technology, we've been able to make a steam generator more compact than ever before. The smaller size fits perfectly on your ironing board for convenience and carrying it around is made far easier. Plus your steam generator iron will take up much less storage space.

Safe carry lock



Your steam generator iron includes a safe carry lock which securely fastens your iron to its base without the risk of slipping or someone touching the hot soleplate. It ensures safe and easy transportation around the house, to and from storage.

Safety auto off



The safety auto off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you safety peace of mind.

Smart Calc clean



Regular descaling protects your iron and maintains steam performance. The Smart Calc-Clean system is an integrated descaling and

cleaning function to extend the lifespan of your steam generator iron. The iron will remind you with both light and sound that cleaning and descaling is needed. Simply place your iron onto the Smart Calc-Clean container and start the process. It takes approx. 2 minutes for the dirty water and scale to be collected, your steam generator will beep once it's done and ready to use again.

SteamGlide Ceramic soleplate



The SteamGlide ceramic soleplate is durable and non-stick, with high scratch resistance and a smooth glide over fabrics. Plus it's easy to clean, especially compared to aluminum soleplates.

Ultra powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even rough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.

Specifications

Easy to use

Cord freedom (swivel): 360 degree cord freedom
Extra large filling hole
Extra stable heel rest
Heat up time: 2 min
Hose length: 1.6 m
Power cord length: 1.8 m
Ready to use: Light indicator, Sound indicator
Refill any time during use
Safety auto off
Soleplate scratch resistance: 3 stars

Accessories included

Calc clean container
Fabric Shaver

Fast crease removal

Power: 2400 W
Pressure: Max 5 bar pump
Ready to use: 2 min
Steam boost: Up to 180 g
Steam-on-demand
Continuous steam: up to 110 g/min
Voltage: 220 - 240 V
Variable steam levels
Vertical steam

Guarantee

2 year worldwide guarantee

Scale management

Descaling and cleaning: Smart Calc Clean
Descaling reminder: Light, Sound, Yes

Size and weight

Packaging dimensions (WxHxL): 26.4 x 30.3 x 40.4 cm
Product dimensions (WxHxL): 19.8 x 21.7 x 34.6 cm
Weight of iron: 1.1 kg
Weight of iron + base: 2.6 kg

Storage

Carry lock: For transportation and safety
Cord storage: Velcro fix
Hose storage: Hose storage compartment

Technology

ProVelocity steam engine

