

PHILIPS

Steam generator
iron

FastCare Compact

Max 5.2 bar pump pressure

Up to 200 g steam boost

1.3-l fixed water tank

GC6704/36



Iron faster with 2 x more steam*

Compact and lightweight, providing powerful continuous steam, the PerfectCare Compact steam generator iron makes fast work of all your ironing.

Fast and powerful

- Powerful steam for ultimate crease removal
- Calc-clean container included — no cartridges, no extra cost
- Ceramic soleplate for durability and easy gliding

Compact and convenient

- Lightweight and compact for easy use and storage
- Large tank for long use

Highlights

Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

Smart descaling



Our built-in descaling system, Smart Calc Clean, reminds you when you need to descale. It also includes a container to make descaling easy. This means no cartridges are required and there are no additional costs.

Ceramic soleplate



Our durable ceramic soleplate glides well on all garments. It is non-stick, scratch-resistant and simple to keep clean.

1.3-l water tank



A 1.3-litre transparent tank gives you more than 1 hour of continuous use. See clearly how much water is left and refill easily at any time under the tap through the large filling door.

Compact and convenient



The lightweight, compact size is perfect for storage and fits conveniently on your ironing board. Exclusive ProVelocity technology makes our steam generators smaller and more compact than ever.

Specifications

Technology

ProVelocity steam engine

Fast crease removal

Continuous steam: Up to 110 g/min

Power: 2400 W

Pressure: Max 5.2-bar pump

Ready to use: 2 min

Steam boost: Up to 200 g

Steam-on-demand

Vertical steam

Voltage: 220-240 V

Easy to use

Soleplate gliding performance: 3 stars

Soleplate name: Ceramic

Water tank capacity: 1300 ml

Hose length: 1.6 m

Power cord length: 1.65 m

Ready to use: Light indicator, Sound indicator

Refill anytime during use

Soleplate scratch resistance: 3 stars

Tap water suitable

Scale management

Descaling and cleaning: Smart Calc Clean

Descaling reminder: Light, Sound, no

cartridges needed, no extra

Accessories included

Calc clean container

Storage

Cord storage: Cord storage compartment

Hose storage: Hose storage compartment

Size and weight

Packaging dimensions (W x H x D): 25 x 27 x 40 cm

Product dimensions (W x H x D): 21 x 23 x 35.4 cm

Total weight with packaging: 4.1 kg

Weight of iron: 1.25 kg

Weight of iron + base: 2.9 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Product packaging: 100% recyclable

