

# PHILIPS

Steam generator  
iron

PerfectCare  
Compact Essential

Max 5.5 bar pump pressure

Up to 280 g steam boost

1.3 L fixed water tank

Carry lock

GC6833/30



## Iron faster with 2x more steam\*

Guaranteed not to burn\*

Powerful, continuous steam works faster than a steam iron – with no temperature or steam settings required thanks to OptimalTEMP technology. Compact and lightweight for easy storage.

### **No temperature setting needed, guaranteed no burn**

- OptimalTEMP technology, no temperature settings required
- No burns – guaranteed

### **Fast & powerful**

- Powerful steam for ultimate crease removal
- SteamGlide Plus soleplate for ultimate gliding
- Calc-clean container included – no cartridges, no extra cost

### **Compact & convenient**

- Lightweight and compact for easy use and storage
- Large tank for long use
- Carry lock for safe and easy transport
- Automatic shut-off when the iron is left unattended

# Highlights

## Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

## No temperature setting needed



Iron everything from jeans to silk without adjusting the temperature. Thanks to OptimalTEMP, no dial or settings are needed. So there's no more pre-sorting the laundry, or waiting for the iron to heat up and cool down. You're ready for any fabric, anytime.

## Safety carry lock



Lock your iron securely to the base station for easy carrying around the house and to reduce the risk of accidentally touching the hot soleplate.

## 1.3 L water tank



A 1.3-liter transparent tank gives you more than 1 hour of continuous use. See clearly how much water is left and refill easily at any time under the tap through the large filling door.

## Smart descaling



Our built-in descaling system, Smart Calc Clean reminds you when you need to descale. It includes a container to make descaling easy. This means no cartridges are required and no additional costs.

## Compact and convenient



The lightweight, compact size is perfect for storage and fits conveniently on your ironing board. Exclusive ProVelocity technology makes our steam generators smaller and more compact than ever.

## No burns – guaranteed



Thanks to OptimalTEMP technology, we guarantee this iron will never cause burns to any ironable fabric. You can even leave it resting face down on your clothes or ironing board. No burns, no shine. Guaranteed.

## SteamGlide Plus soleplate



Our exclusive SteamGlide Plus soleplate – with its advanced titanium layer and 6-layer coating – delivers ultimate gliding performance over any fabric. Non-stick, scratch-resistant and easy to keep clean.

## Auto shut off



The automatic shut off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind.

# Specifications

## Technology

For all ironable fabrics  
No burns  
No temperature settings needed  
OptimalTEMP technology  
ProVelocity steam engine

## Fast crease removal

Continuous steam: Up to 110 g/min  
Power: 2400 W  
Pressure: Max 5.5. bar pump  
Ready to use: 2 min  
Steam boost: Up to 280 g  
Voltage: 220-240 V

## Easy to use

Safe on all ironable fabrics: Even delicates like silk  
Soleplate gliding performance: 5 stars  
Soleplate name: SteamGlide Plus

Water tank capacity: 1300 ml  
Hose length: 1.6 m  
Power cord length: 1.65 m  
Ready to use: Light indicator, Sound indicator  
Refill any time during use  
Safety auto off  
Soleplate scratch resistance: 4 stars  
Tap water suitable

## Scale management

Descaling and cleaning: Smart Calc Clean  
Descaling reminder: Light, Sound, no cartridges needed, no extra

## Accessories included

Calc clean container

## Storage

Carry lock: For transportation and safety  
Cord storage: Cord storage compartment  
Hose storage: Hose storage compartment

## Size and weight

Packaging dimensions (WxHxL): 23.5 x 27 x 39.8 cm  
Product dimensions (WxHxL): 20.1 x 22.2 x 38.4 cm  
Total weight with packaging: 3.7 kg  
Weight of iron: 1.3 kg  
Weight of iron + base: 2.72 kg

## Guarantee

2 year worldwide guarantee

## Green efficiency

Product packaging: 100% recycable

