

# PHILIPS

Steam generator  
iron

PerfectCare Pure

Max 5 bar pump pressure

180 g steam boost

1.5 L fixed watertank

GC7619/21



## Faster and easier ironing

with no temperature adjustment required

Iron your garments without adjusting temperature thanks to the revolutionary OptimalTEMP technology. Much more compact and light weight design for easier storage. Use demineralized water only for the best performance of your appliance.

### Carefree ironing, no temperature setting required

- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board

### Fast and powerful ironing

- Max 5 bar pump pressure
- 1.5 L water tank, up to 2 hours of ironing
- Saving energy with ECO mode
- The most compact and lightest steam generator
- Our best gliding soleplate



# Highlights

## OptimalTEMP technology



"Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Compact ProVelocity steam engine delivers more steam for ironing faster. It enables compact design of your steam generator for easier storage"

## Safe rest



The Philips innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. During ironing, no need to put your iron back to the base station, just leave the hot iron soleplate directly on the garments or cotton ironing board cover without additional resting accessory. It will not damage any of your ironable garments, neither the board. This makes your ironing easier with less wrist efforts.

## T-ionicGlide soleplate



Our best gliding and most scratch resistant, 5star rated soleplate with integrated Titanium-Oxide layer

## Energy saving



By using the ECO mode, with reduced amount of steam, you can save energy without compromising on the ironing results. For faster ironing, switch to Turbo mode, which generates more steam.

## 1.5 L water tank



Thanks to the 1.5 L watertank capacity, you can iron up to 2 hours continuously without any refills. The large filling hole makes the refilling fast. You can either fill your steam generator iron under the tap or use a jug / large bottle.

## Max 5 bar pump pressure



The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

## Compact and light

The compact design makes your appliance easy to storage. Space will never be an issue again! As it is very light, your appliance is easy to carry. Its light weight iron will make your ironing much more comfortable.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Calc management

Calc clean solution: Demineralized water

## Easy to use

Cord freedom (swivel): 180 degree cord freedom

Cord storage: Cord clip

Heat up time: 2 min

Hose length: 1.6 m

Hose storage: Hose storage compartment

Power cord length: 1.8 m

Refill any time

Safe for all fabrics: Even for delicates like silks

Water tank capacity: 1500 ml

Filling and emptying water: Extra large filling hole

## Fast & powerful crease removal

Continuous steam output: 120 g/min

OptimalTEMP technology

Power: 2400 W

Safe rest

Soleplate: T-ionicGlide

Steam boost: 180 g

Steam tip

Variable steam settings

Vertical steaming

Turbo steam

Pressure: Max 5 bar pump pressure

## Sustainability

Energy saving mode

## Technical specifications

Voltage: 220- 240 V

## Weight and dimensions

Packaging dimensions (WxHxL): 40 x 23 x 28 cm

Product dimensions (WxHxL): 35.4 x 19.3 x 22.4 cm

Weight of iron: 1.2 kg

Weight of iron + base: (with 1 cartridge) 3.19 kg

