

# PHILIPS

Steam generator  
iron

PerfectCare Pure

Max 5 bar pump pressure

220 g steam boost

1.5 L fixed watertank

GC7630/30



## Faster and easier ironing

with no temperature adjustment required

Iron your garments without adjusting temperature thanks to the revolutionary OptimalTEMP technology. Much more compact and light weight design for easier storage. 99% calc free, Pure Steam anti-scale cartridges increase life by 5 times

### Carefree ironing, no temperature setting required

- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board

### Fast and powerful ironing

- Max 5 bar pump pressure
- Tap water friendly, refill anytime during ironing
- Steam boost up to 220 g
- 1.5 L water tank, up to 2 hours of ironing
- Our best gliding soleplate
- Saving energy with ECO mode
- 99% calc-free with PureSteam Anti-scale cartridge
- The most compact and lightest steam generator



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## OptimalTEMP technology



"Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Compact ProVelocity steam engine delivers more steam for ironing faster. It enables compact design of your steam generator for easier storage"

## Energy saving



By using the ECO mode, with reduced amount of steam, you can save energy without compromising on the ironing results. For faster ironing, switch to Turbo mode, which generates more steam.

## Max 5 bar pump pressure



The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

## Refill tap water any time



Your steam generator iron is designed to use tap water. While ironing, when you run out of water in the watertank, you can refill it easily without waiting or turning your appliance off.

## Safe rest



The Philips innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. During ironing, no need to put your iron back to the base station, just leave the hot iron soleplate directly on the garments or cotton ironing board cover without additional resting accessory. It will not damage any of your ironable garments, neither the board. This makes your ironing easier with less wrist efforts.

## Steam boost up to 220 g



The steam boost can be used for vertical steaming and tough creases.

## T-ionicGlide soleplate



Our best gliding and most scratch resistant, 5star rated soleplate with integrated Titanium-Oxide layer

## 1.5 L water tank



Thanks to the 1.5 L watertank capacity, you can iron up to 2 hours continuously without any refills. The large filling hole makes the refilling fast. You can either fill your steam generator iron under the tap or use a jug / large bottle.

## 99% calc-free

PureSteam Anti-scale cartridge filters 99% of scale from tap water. It ensures consistent steam flow and prevents calc residues on clothes.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Fast & powerful crease removal

OptimalTEMP technology  
Pressure: Max 5 bar pump pressure  
Continuous steam output: 120 g/min  
Steam boost: 220 g  
Soleplate: T-ionicGlide  
Safe rest  
Variable steam settings  
Vertical steaming  
Turbo steam  
Steam tip  
Power: 2400 W

## Easy to use

Heat up time: 2 min  
Refill any time  
Safe for all fabrics: Even for delicates like silks

Water tank capacity: 1500 ml  
Filling and emptying water: Extra large filling hole  
Power cord length: 1.8 m  
Cord storage: Cord clip  
Hose length: 1.6 m  
Hose storage: Hose storage compartment  
Cord freedom (swivel): 180 degree cord freedom

## Sustainability

Energy saving mode

## Calc management

Suitable for tap water  
Calc clean reminder  
Calc clean solution: Demineralized water, PureSteam Anti-scale cartridge

## Technical specifications

Weight of iron: 1.2 kg  
Weight of iron + base: (with 1 cartridge) 3.19 kg  
Product dimensions: 35.4 x 19.3 x 22.4 cm  
Packaging dimensions: 40 x 23 x 28 cm  
Voltage: 220- 240 V

## Accessories

Extra anti-calc cartridges

