

Philips PerfectCare
Compact
Refurbished Steam
generator iron

Refurbished product

Max 5.3 bar pump pressure
Up to 280 g steam boost
1.5-l water tank capacity

GC7808



Iron faster with 2 x more steam*

Philips' most compact steam generator

Philips PerfectCare Compact Iron your garments faster thanks to powerful continuous steam. No need to adjust the temperature between garments thanks to OptimalTEMP technology. Enjoy a compact and lightweight design for easier storage.

No temperature setting needed; no burning, guaranteed

- Go from ironing jeans to silk; no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board

Fast ironing with continuous powerful steam

- Integrated easy-clean system for long-lasting performance
- Superior gliding soleplate and scratch resistance
- Save energy with ECO mode
- Powerful steam for ultimate crease removal

Compact technology

- Lightweight and compact size for easy storage
- Large water tank for longer continuous use
- Safe and secure carry lock

PHILIPS

Highlights

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron all fabrics, from jeans to silk, with no burning guaranteed thanks to the perfect combination of temperature and continuous powerful steam.

Safe rest



Innovative OptimalTEMP technology guarantees no burning on any ironable fabric. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

Smart Calc clean



Regular descaling protects your iron and maintains steam performance. The Smart Calc-Clean system is an integrated descaling and cleaning function to extend the lifespan of your steam generator iron. The iron will remind you with both light and sound that cleaning and descaling is needed. Simply place your iron onto the Smart Calc-Clean container and start the process. It takes approx. 2 minutes for the dirty water and scale to be collected; your steam generator will beep once it's finished and ready to use again.

SteamGlide soleplate



The SteamGlide soleplate is durable and non-stick, with great scratch resistance and a smooth glide over fabrics. Plus it's easy to clean, especially compared to aluminium soleplates.

Energy saving



ECO mode allows you to save energy without compromising your ironing results. The ECO mode uses a reduced amount of steam, but still a sufficient amount to iron all your garments.

Ultra-powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even tough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.

Specifications

Technology

- For all ironable fabrics
- No burns
- No temperature settings needed
- OptimalTEMP technology
- ProVelocity steam engine
- Smart Control Processor

Fast crease removal

- Continuous steam: Up to 120 g/min
- Power: 2400 W
- Pressure: max 5.3-bar pump
- Ready to use: 2 min
- Steam boost: Up to 280 g
- Steam-on-demand
- Variable steam levels
- Vertical steam
- Voltage: 220-240 V

Easy to use

- Safe on all ironable fabrics: Even delicates like silk
- Soleplate gliding performance: 4 stars
- Soleplate name: SteamGlide
- Water tank capacity: 1500 ml
- Cord freedom (swivel): 180 degree cord freedom
- Hose length: 1.6 m
- Integrated power plug
- Power cord length: 1.8 m
- Precision steam tip
- Ready to use: Light indicator, Sound indicator
- Refill anytime during use
- Safety auto off
- Soleplate scratch resistance: 4 stars
- Tap water suitable

Scale management

- Descaling and cleaning: Smart Calc Clean
- Descaling reminder: Light, Sound, no cartridges needed, no extra

Storage

- Carry lock: For transportation and safety
- Cord storage: Velcro fix
- Hose storage: Hose storage compartment

Accessories included

- Calc clean container

Size and weight

- Packaging dimensions (W x H x D): 23 x 27.5 x 39.3 cm
- Product dimensions (W x H x D): 19.3 x 22.3 x 37.3 cm
- Total weight with packaging: 3.85 kg
- Weight of iron: 1.2 kg
- Weight of iron + base: 2.95 kg

Guarantee

- 2 year worldwide guarantee

Green efficiency

- Energy saving mode
- Energy saving*: 30 %
- Recycled plastic used: 30 %
- User manual: 100% recycled paper

Calc management

- Calc clean solution: Demineralised water



Issue date 2020-02-20

Version: 1.0.1

12 NC: 0000 041 02006
EAN: 87 10895 68383 8

© 2020 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Up to 30% energy saving with ECO mode compared to Turbo mode
based on IEC 60311

* Compared to Philips steam iron Azur Performer