

PHILIPS

Steam generator
iron

PerfectCare
Compact Plus

Max 6.5-bar pump pressure

Up to 450 g steam boost

1.5 l detachable water tank

Carry lock



GC7933/36



Finish ironing 30 minutes faster

Compared to Philips steam iron Azur*

So fast and convenient, and you'll never worry about burning clothes. Finish faster with twice as much steam as a steam iron. No settings to change and faster results with better wrinkle removal. Easy to iron your whole basket in one go.

OptimalTEMP technology, no settings required

- Guaranteed no burns
- No temperature settings to change

Fast and powerful

- Powerful steam for ultimate crease removal
- Scratch-resistant SteamGlide Plus soleplate for smooth glide
- Calc-clean container included - no cartridges, no extra cost

Compact and convenient

- Lightweight and compact for easy use and storage
- Large detachable water tank for easy refilling
- Safe and easy auto shut-off
- Carry lock for safe and easy transport

Highlights

Guaranteed no burns



Even if you're multi-tasking or get distracted, you'll never burn your clothes. Thanks to our OptimalTEMP technology, we promise this steam generator iron will never burn any ironable fabric. You can even leave it resting face down on your clothes or ironing board. No burns, no shine. Guaranteed.

Ultra-powerful steam



When you need to tackle tough creases with ease, rely on our continuous steam to do the hard work for you. Watch those creases melt away when you use an extra boost of steam where you need it. And it's perfect when you want to steam vertical curtains or refresh hanging clothes.

Compact and convenient



Thanks to its compact size it's light and easy to handle as you iron your clothes. It even fits on your ironing board. But don't think smaller means less powerful. Thanks to our exclusive

ProVelocity technology, we've made powerful steam generators that are lightweight and more compact than ever.

1.5 l detachable water tank



A 1.5 litre transparent tank gives you up to 1.5 hours of continuous use. See clearly how much water is left and refill easily at any time under the tap through the large filling door.

Easy descaling



It's easy to maintain your steam generator with Smart Calc Clean, our built-in descaling system. It will remind you when it's time to descale and includes a container to make descaling easy and safe. Since it is reusable you will save money and never need to buy extra cartridges.

No settings to change



Save a step in your weekly ironing routine. You won't need to separate fabrics or change settings and wait for the temperature to change

any more. Thanks to OptimalTEMP, you iron everything from your denim jeans to delicate silks without adjusting the temperature.

SteamGlide Plus



Our scratch-resistant SteamGlide Plus soleplate delivers excellent gliding performance on any fabric. Our patented 5 layer coating with its advanced titanium layer effortlessly glides on any fabric for the fastest results.

Safety carry lock



Lock your iron securely to the base station for easy carrying around the house and to reduce the risk of accidentally touching the hot soleplate.

Safe and easy auto shut-off



The automatic shut-off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind.

Specifications

Technology

For all ironable fabrics
No burns
No temperature settings needed
OptimalTEMP technology
ProVelocity steam engine

Fast crease removal

Continuous steam: Up to 120 g/min
Power: 2400 W
Pressure: Max 6.5-bar pump
Ready to use: 2 min
Steam boost: Up to 450 g
Steam-on-demand
Vertical steam
Voltage: 220-240 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk
Soleplate gliding performance: 4 stars
Soleplate name: SteamGlide Plus
Water tank capacity: 1500 ml

Detachable water tank

Hose length: 1.6 m
Integrated power plug
Power cord length: 1.65 m
Precision steam tip
Ready to use: Light indicator, Sound indicator
Refill anytime during use
Soleplate scratch resistance: 4 stars
Tap water suitable
Auto shut-off

Scale management

Descaling and cleaning: Smart Calc Clean
Descaling reminder: Light, Sound

Storage

Carry lock: For transportation and safety
Cord storage: Velcro fix
Hose storage: Hose storage compartment

Accessories included

Calc clean container

Size and weight

Packaging dimensions (W x H x D): 23 x 26.5 x 42.6 cm
Product dimensions (W x H x D): 20 x 23.3 x 37.1 cm
Total weight with packaging: 3.85 kg
Weight of iron: 1.3 kg
Weight of iron + base: 2.8 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving*: 35 %
Product packaging: 100% recyclable
Recycled plastic used: 15 %
User manual: 100% recycled paper

Design

Colour: Purple Magic

