

# PHILIPS

Pressurised steam  
generator

8400 series

1.6 L

GC8420



## Great results, minimum effort

No compromise.

Powerful yet surprisingly convenient, this ironing system produces continuous steam with high pressure. The large detachable watertank you can refill at any time and anywhere, making ironing fast and easy.

### **Fast and powerful ironing**

- Up to 5 bar pressure
- Continuous steam up to 110 g/min
- Steam boost up to 160 g
- SteamGlide soleplate is Philips premium soleplate

### **Comfortable ironing**

- Detachable watertank
- Detachable 1.6 L watertank
- Heat-resistant mat: to safely place your hot iron on

### **Easy set up and storage**

- Ready to use in 2 minutes with unlimited refill
- Lock your iron securely to the base station
- Integrated cord and hose storage compartment

# Highlights

## Up to 5 bar pressure



The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

## Steam boost up to 160 g



The steam boost can be used for vertical steaming and tough creases.

## Detachable 1.6 L watertank



A large watertank capacity enables you to iron with steam without having to refill. The tank can hold a large amount of water so you can

iron up to 3 hours uninterrupted. Being detachable, you can easily re-fill the tank any time. It gives you endless, powerful steam.

## Iron resting mat



To improve comfort during ironing you can place the iron everywhere with the heat resistant iron resting mat. As you do not need to put the iron on its heel during intervals, you decrease the straining of your wrist. The resting mat is highly heat resistant, even when a soleplate heated to 250 °C is placed on it.

## Safety carry lock



Your steam generator iron comes with a safety carry lock. You can lock your iron safely on the base, making it safer, reducing the risk of people touching the hot soleplate. You can also carry the steam generator easily.

# Specifications

## Accessories

**Included in pack:** Heat resistant iron resting mat

## Comfortable ironing

**Anti-scale management:** Easy Rinse

**Cord length:** 1,8 m

**Ergonomic iron design:** Ergonomically designed iron for comfortable ironing

**Hose length:** 1,9 m

**Safe in use:** Overheat safety stop

**Suitable for tap water**

## Crease removal

**Continuous steam:** Up to 110 gr/min

**Pressurised Steam:** Up to 5 bar

**Soleplate:** Optimal vent pattern

**Steam Boost:** Up to 160 gr/min

**Vertical Steam:** Continuous vertical steam

## Easy to use

**Control:** Steam ready light, Temperature ready light, Variable steam settings, Water tank empty light

**Easy to set up and store:** Carry-lock, Easy cord and hose storage

**Reaching tricky areas:** Button groove, Steam tip

**Water tank:** Detachable

## Smooth gliding

**Soleplate:** SteamGlide soleplate

## Technical specifications

**Boiler wattage:** 1200 W

**Frequency:** 50-60 Hz

**Iron wattage:** 800 W

**Start-up time:** 2 minute(s)

**Voltage:** 220-240 V

