

# PHILIPS

Pressurised steam  
generator

8500 series

1.6 L

GC8510



## Great results, minimum effort

### Iron without compromise

Powerful yet surprisingly convenient iron. This Philips ironing system produces continuous steam with high pressure. The large detachable watertank you can refill at any time and anywhere, making ironing fast and easy.

#### Fast and powerful ironing

- Continuous steam up to 120 g/min
- Up to 5 bar pressure
- 150 g steam boost to remove stubborn creases easily

#### Comfortable ironing

- SteamGlide soleplate is Philips premium soleplate
- Ergonomically and lightweight 1.2kg iron

#### Easy to use

- Detachable 1.6 L watertank

#### Save energy consumption

- Save 20% energy and 40% water consumption

#### Hassle-free scale removal

- Permanent anti-calc tablets inside delay scale build up
- Easy rinsing without accessories

# Highlights

## Up to 5 bar pressure



The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.

## Steam boost up to 150 g




The iron's 150 g steam boost enables you to easily remove even the most stubborn creases.

## Continuous steam



The more steam, the faster the ironing. The unique technology in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

## Ergonomic iron




The ergonomic design of the iron facilitates comfortable ironing by putting less strain on the wrist. The upward sloping handle ensures a natural position reducing strain during ironing. The iron design also prevents the repetitive movements caused by placing an iron on its heel. The iron is light (1.2kg) for an easy & comfortable ironing experience.

## SteamGlide soleplate



SteamGlide soleplate is the best Philips soleplate for your steam iron. It has great scratch resistancy, glides excellent and is easy to clean.


## Detachable 1.6 L watertank



A large watertank capacity enables you to iron with steam without having to refill. The tank can hold a large amount of water so you can

iron up to 3 hours uninterrupted. Being detachable, you can easily re-fill the tank any time. It gives you endless, powerful steam.

## Anti-calc Tablets



Permanent anti-calc tablets delay the formation of scale build up ensuring better protection for your system iron

## Easy Rinsing

In order to improve the lifetime of your system iron we recommend to rinse the inside of your system base. This has been made easily accessible with the easy rinse knob. You don't need any accessories to rinse your system iron.

## Eco-setting



Save 20% energy and 40% water consumption by selecting the eco-setting on your Philips Iron. The eco-setting offers the most energy efficient way to obtain perfect ironing results.

# Specifications

## Fast & powerful crease removal

Soleplate: SteamGlide  
Steam output  
Continuous steam output: 120 g/min  
Steam boost: 150 g  
Vertical steaming  
Pressure: Up to 5  
Variable steam settings  
Steam tip  
Power: 2200 W

## Easy to use

Water tank capacity: 1600 ml  
Filling and emptying water: Detachable water tank  
Refill any time  
Heat up time: 2 min  
Storage solution: Carry lock  
Hose storage: Hose clip  
Power cord length: 1.8 m  
Cord freedom (swivel): 180 degree cord freedom  
Hose length: 1.9 m

## Sustainability

Energy saving: 20% energy reduction

## Calc management

Suitable for tap water  
Calc clean solution: Anti-calc tablets + rinsing  
Calc clean reminder

## Technical specifications

Voltage: 220 - 240 V  
Weight of iron: 1.2 kg  
Weight of iron + base: 5.2 kg

