

PHILIPS

Steam generator
iron

PerfectCare Aqua

Max 5.3 bar pump pressure

Up to 260 g steam boost

2.5 L fixed watertank

GC8624/20



Ultra fast ironing

with no temperature adjustment required

Iron any ironable garment from silk, to linen, to cotton, to cashmere...in any order, without having to adjust. Your Philips PerfectCare Iron delivers fast results without risk of burn or shine for all your garments. Truly simple ironing.

No temperature setting needed, guaranteed no burn

- Iron jeans to silk, no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- Easy and efficient descaling system
- Philips best gliding with increased scratch resistance
- Save energy with ECO mode

Ultimate ironing experience

- Extra-large water tank for longer continuous use



asimpleswitch.com

Highlights

2.5 L water tank




The water tank has an extra-large 2.5 L capacity, so you get the convenience of up to 3 hours of continuous use, with no need to top-up the tank. It's also transparent, so you can get a 360° view of the tank to easily see how much water you have left to continue creating steam efficiently. When you do need to refill, your steam generator iron has a large filling hole that allows you to easily fill the water tank under the tap, or alternatively with a jug or bottle at any time during ironing.

Easy De-Calc




Regular descaling protects your iron and ensures you'll continue to get the very best steam performance. The exclusively designed and ideally positioned Easy De-Calc Plus function provides the ideal way to get rid of lime scale and extend the lifespan of your steam generator iron. The iron will remind you with both light and sound when it's time to clean and descale. Then when your appliance is cold, simply remove the Easy De-Calc knob, collect the dirty water and scale into a cup and discard.

Energy saving



ECO mode allows you to save energy without compromising your ironing results. The ECO mode uses a reduced amount of steam, but still a sufficient amount to iron all your garments.

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron fabrics from jeans to silk, with guaranteed no burns thanks to the perfect combination of temperature and continuous powerful steam.

Safe rest



Innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

SteamGlide Plus soleplate



The SteamGlide Plus soleplate is durable and non-stick is based on the ceramic finishing. It has an integrated titanium oxide layer for superior gliding performance.

Ultra powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even rough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Easy to use

Cord freedom (swivel): 180 degree cord freedom

Heat up time: 2 min

Hose length: 1.7 m

Power cord length: 1.8 m

Water tank capacity: 2500 ml

Fast crease removal

Power: 2400 W

Pressure: max 5.3 bar

Steam boost: up to 260 g

Voltage: 220–240 V

