



Philips PerfectCare Aqua
Steam generator iron

5.8 bar

300 g steam boost
Carry lock
2.5 L fixed watertank

Ultra fast ironing

with no temperature adjustment required

Iron any ironable garment from silk, to linen, to cotton, to cashmere...in any order, without having to adjust. Your Philips PerfectCare Iron delivers fast results without risk of burn or shine for all your garments. Truly simple ironing.



GC8625/30

Carefree ironing, no temperature setting required

- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board
- Tested and approved by independent textile experts

Fast and powerful ironing

- Tap water friendly, refill anytime during ironing
- Steam boost up to 300 g
- Ready to use in 2 minutes with unlimited refill
- Large 2.5 L fully visible water tank
- Saving energy with ECO mode
- Lock your iron securely to the base station
- Descale effectively and easily your appliance to prolong it
- New SteamGlide soleplate is Philips premium soleplate



asimpleswitch.com

PHILIPS

Steam generator iron
5.8 bar 300 g steam boost, Carry lock, 2.5 L fixed watertank

GC8625/30

Highlights

OptimalTEMP technology



Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Powerful Cyclonic steam chamber which delivers powerful consistent steam, making ironing easier and faster.

Energy saving



By using the ECO mode, with reduced amount of steam, you can save energy without compromising on the ironing results.

Steam boost up to 300 g

The steam boost can be used for vertical steaming and tough creases.

Refill tap water any time




Your steam generator iron is designed to use tap water. While ironing, when you run out of water in the watertank, you can refill it easily without waiting or turning your appliance off.

Steam ready in 2 minutes



Steam is ready to use in 2min and can be refilled at anytime during ironing.

Tested and approved:



This iron is tested and approved by independent textile experts institutes for its excellent ironing performance, such as DWI,

IWTO, Woolmark. The Woolmark Apparel Care program helps consumers identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips with its exclusive OptimalTEMP technology has been so far the only brand able to be certified with the Gold standard from Woolmark. You can be confident that the Woolmark-approved apparel care products are ideally suited for any wool garments.

Easy De-Calc



Ultra long lasting steam performance: Philips' exclusive Easy De-Calc function provides the ideal way to get rid of limescale and extend the lifetime of your steam generator iron. Your iron will remind you with light and sound when to perform cleaning. Only when your appliance is cold, simply open the Easy De-Calc knob, and collect the dirty water and scale in a cup.



Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Calc management

- Calc clean reminder
- Calc clean solution: Easy De-calc
- Suitable for tap water

Easy to use

- Cord freedom (swivel): 180 degree cord freedom
- Cord storage: Cord clip
- Heat up time: 2 min
- Hose length: 1.7 m
- Hose storage: Hose storage compartment
- Power cord length: 1.8 m
- Refill any time
- Safe for all fabrics: Even for delicates like silks
- Storage solution: Carry lock

- Water tank capacity: 2500 ml
- Filling and emptying water: Extra large filling hole

Fast & powerful crease removal

- OptimalTEMP technology
- Power: 2400 W
- Safe rest
- Soleplate: SteamGlide Plus
- Steam boost: 300 g
- Steam tip
- Variable steam settings
- Vertical steaming
- Pressure: Up to 5.8 bar pressure

Technical specifications

- Voltage: 220- 240 V



Issue date 2016-09-26

Version: 4.1.1

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com