

# PHILIPS

Steam generator  
iron

PerfectCare  
Performer

Max 6.2 bar pump pressure

Up to 390 g steam boost

SoftGrip

1.8 L detachable watertank



GC8723/00



## Powerful continuous steam for ultra faster ironing

### 1.8 L detachable water tank

Philips PerfectCare Performer steam generator iron ensures a true simple, powerful, and no burn ironing experience. The powerful continuous steam penetrates deeply and continuously into the fibre to remove creases easily.

#### Carefree ironing, no temperature setting required

- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board

#### Fast and powerful ironing

- SoftGrip: Amazing comfortable handle
- CompatProVelocity Steam Engine: all the time continuous steam
- Continuous steam up to 120 g/min
- 1.8 L detachable water tank, up to 2 hours of ironing
- Tap water friendly, refill anytime during ironing
- Smart Calc clean system with sound&light Calc Clean reminder
- Ready to use in 2 minutes with unlimited refill
- Saving energy with ECO mode
- Lighter weight steam generator from Philips
- Max 6.2 bar pump pressure

# Highlights

## 1.8 L detachable water tank

The watertank can be removed to be refilled easily under the tap. The large filling hole makes the refilling fast. Thanks to the 1.8 L watertank capacity, you can iron up to 2 hours continuously without any refills.

## ProVelocity Steam Engine

Water is transferred from the water tank to the iron by a high pressure pump. A lot of water travels inside of steam chamber at very high speed. It enables very powerful and constant steam all the time to come out from the soleplate without water condensation;

## Continuous steam

The more steam, the faster the ironing. The unique technology in a Philips steam generator iron generates powerful steam making ironing easier, better and faster.

## Energy saving

By using the ECO mode, with reduced amount of steam, you can save energy without compromising on the ironing results.

## Lighter weight steam generator

Thanks to the revolutionary ProVelocity technology, we made your steam generator iron more compact than ever before. The compact steam generator fits easily on your ironing board making your ironing more convenient. In addition, your steam generator takes much less storage space.

## OptimalTEMP technology

"Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Compact ProVelocity steam engine delivers more steam for ironing faster. It enables compact design of your steam generator for easier storage"

## Refill tap water any time

Your steam generator iron is designed to use tap water. While ironing, when you run out of water in the watertank, you can refill it easily without waiting or turning your appliance off.

## Safe rest

The Philips innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. During ironing, no need to put your iron back to the base station, just leave the hot iron soleplate directly on the garments or cotton ironing board cover without additional resting accessory. It will not damage any of your ironable garments, neither the board. This makes your ironing easier with less wrist efforts.

## Smart Calc Clean system

Smart Calc Clean system is an integrated descaling and cleaning function to protect your steam generator iron. After each about 10 hour ironing, you will be reminded by the sound and light of your steam generator iron to perform calc clean process. The Calc Clean Container will provide you the convenience during the Calc Clean process, by just resting your iron on the container without holding your iron to stress your waist. After cleaning process, all the dirty water is collected in the container, your steam generator iron is ready to use again.

## Steam ready in 2 minutes

Steam is ready to use in 2min and can be refilled at anytime during ironing.

## Max 6.2 bar pump pressure

The more steam, the faster the ironing. Powerful continuous steam is generated which penetrates deep inside the garments making ironing faster and better. Steam amount can be regulated to fit your needs.

## Amazing comfortable handle

The soft material finishing applied on the top of the ironing handle delivers a soft touch. The special pattern to enhance the gripping experience making gripping more comfortable during ironing

# Specifications

## Technology

For all ironable fabrics  
No burns  
OptimalTEMP technology  
ProVelocity steam engine  
Smart Control Processor

## Fast crease removal

Continuous steam: Up to 120 g/min  
Power: 2400 W  
Pressure: Max 6.2 bar pump  
Ready to use: 2 min  
Steam boost: Up to 390 g  
Steam-on-demand  
Variable steam levels  
Vertical steam

## Easy to use

Safe on all ironable fabrics: Even delicates like silk  
Soleplate gliding performance: 5 stars  
Soleplate name: SteamGlide Plus  
Detachable water tank  
Hose length: 1.6 m  
Power cord length: 1.8 m  
Precision steam tip  
Ready to use: Light indicator, Sound indicator  
Refill any time during use  
Safety auto off  
Soft grip  
Soleplate scratch resistance: 4 stars

## Scale management

Descaling and cleaning: Smart Calc Clean  
Descaling reminder: Light, Sound, Yes

## Storage

Carry lock: For transportation and safety  
Cord storage: Velcro fix, Yes  
Hose storage: Hose storage compartment

## Size and weight

Product dimensions (WxHxL): 22 x 24 x 37 cm  
Weight of iron: 1.22 kg  
Weight of iron + base: 3.2 kg

## Guarantee

2 year worldwide guarantee

## Green efficiency

Energy saving mode  
Product packaging: 100% recyclable  
User manual: 100% recycled paper

