

Steam generator iron

- Max. 7.5 bar pressure
- Up to 480 g steam boost
- 1.8 L detachable water tank
- Ultra-light iron

GC8942/26

Incredibly light and powerful

for speed and comfort

PerfectCare Expert Plus is designed for your comfort and convenience. Ultra-light and easy to handle, but still with powerful steam to achieve great results faster. With OptimalTEMP technology to guarantee no burns on all ironable garments.

Benefits

No temperature setting needed; no burning, guaranteed

- OptimalTEMP technology, no temperature settings required
- No burns – guaranteed

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- SteamGlide Advanced soleplate, ultimate gliding and durability
- Easy and efficient descaling system for lasting performance
- Save energy with ECO mode

Extra convenience

- Ultra-light weight and comfortable-to-handle iron
- Large 1.8 L detachable water tank for easy refilling
- Carry lock for safe and easy transport
- Automatic shut-off when iron is left unattended

PHILIPS

Features

No temperature setting needed



Iron everything from silk to jeans without adjusting the temperature. Thanks to OptimalTEMP, no dial or settings are needed. So there's no more pre-sorting the laundry, or waiting for the iron to heat up and cool down. You're ready for any fabric, any time.

No burns – guaranteed



Thanks to OptimalTEMP technology, we guarantee that this iron will never cause burns to any ironable fabric. You can even leave it resting face down on your clothes or ironing board. No burns, no shine. Guaranteed.

Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

Ultra-lightweight iron



The iron is amazingly light and comfortable to handle, gliding easily and reducing wrist strain. Its minimal weight also makes it easy and effective for vertical steaming of curtains and hanging clothes.

SteamGlide Advanced soleplate



SteamGlide Advanced is our best soleplate for ultimate gliding performance and maximum scratch resistance. Its stainless steel base is twice as hard as a

regular aluminium base, and our patented 6-layer coating with advanced titanium layer glides effortlessly for the fastest results.

Easy De-calc



Regular descaling protects your iron, extends its lifetime and ensures the best steam performance. Our exclusive Easy De-Calc system collects limescale continuously with an indicator light to tell you when it needs emptying. Simply remove the plug and let the water and scale particles flow out.

1.8 l detachable water tank



1.8-litre transparent tank gives you up to 2 hours of continuous use. When the water tank is empty, you will be reminded by the indicator light and you can refill easily at any time under the tap through the large filling door.

Safety carry lock



Lock your iron securely to the base station for easy carrying around the house and to reduce the risk of accidentally touching the hot soleplate.

Auto shut-off



The automatic shut-off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind.

Energy saving



Save energy and get the same great results. ECO mode reduces your energy consumption for garments that require less steam.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Technology

Cyclonic steam chamber	Yes
For all ironable fabrics	Yes
No burns	Yes
No temperature settings needed	Yes
OptimalTEMP technology	Yes

Fast crease removal

Continuous steam Power	Up to 120 g/min Max 2100 W
Pressure	Max. 7.5 bar
Ready to use	2 min
Steam boost	Up to 480 g
Steam-on-demand	Yes
Vertical steam	Yes
Voltage	220 - 240 V

Easy to use

Safe on all ironable fabrics	Even delicates like silk
Soleplate gliding performance	5 stars
Soleplate name	SteamGlide Advanced
Water tank capacity	1800 ml
Detachable water tank	Yes
Hose length	1.7 m
Low water alert	Yes
Power cord length	1.65 m
Precision steam tip	Yes
Ready to use	Light indicator
Refill anytime during use	Yes
Safety auto off	Yes
Soleplate scratch resistance	5 stars
Tap water suitable	Yes

Scale management

Descaling and cleaning	Easy De-calc
------------------------	--------------

Descaling reminder Light

Storage

Carry lock	For transportation and safety
Hose storage	Hose storage compartment

Size and weight

Packaging dimensions (W x H x D)	31 x 31 x 47 cm
Product dimensions (W x H x D)	23.9 x 26.9 x 42.6 cm
Total weight with packaging	5.5 kg
Weight of iron	0.8 kg
Weight of iron + base	4 kg

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

Energy saving mode	Yes
Energy saving*	45 %
Product packaging	100% recyclable
User manual	100% recycled paper

Packaging dimensions

Height	31.00 cm
Width	31.00 cm
Depth	47.00 cm
Net weight	4.16 kg
Gross weight	5.52 kg
EAN	08710103874959
Number of products included	1
Country of origin	ID
Harmonised Systems Code	851640

* Up to 45% energy saving based on IEC 603311, compared to RI3320 at max. setting



data subject to change
2019, January 24

Version: 9.0.1
EAN: 08710103874959

© 2019 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com