

PHILIPS

Steam generator
iron

PerfectCare Expert

5 bar

230 g steam boost

1.5L detachable water tank

GC9220/27



One perfect setting for all your clothes

Thanks to the revolutionary OptimalTemp technology

Iron any ironable garment from silk, to linen, to cotton, to cashmere...in any order, without having to adjust. Your Philips PerfectCare Iron delivers fast results without risk of burn or shine for all your garments. Truly simple ironing.

One perfect setting for all your clothes

- 100% easy to use, no adjustment required
- 100% safe on all ironable garments
- 100% fast on all fabrics, no other iron is faster
- OptimalTemp: The perfect combination of steam & temperature

Fast and powerful ironing

- 1.5 litre detachable water tank, up to 2 hours of ironing
- Ready to use in 2 minutes with unlimited refill

Comfortable ironing

- Descale effectively and easily your appliance to prolong it
- New SteamGlide soleplate is Philips premium soleplate



asimpleswitch.com



asimpleswitch.com

Highlights

100% easy to use



100% easy to use, no adjustment required. You can now iron all ironable garments one after the other, without having to wait or to adjust the iron's temperature dial.

100% safe




100% safe on all fabrics even the most delicate like silk, cashmere, wool, polyester. Independent iron testing institutes have used PerfectCare on the most sensitive ironable garments and they confirmed the excellence of ironing results.

100% fast

100% fast on the toughest fabrics, no other steam generator is faster from start to finish.

Detachable watertank, 5 bar



1.5 litre detachable water tank for up to 2 hours of ironing without refilling.

Easy De-Calc



Ultra long lasting steam performance: Philips' exclusive Easy De-Calc function provides the ideal way to get rid of limescale and extend the lifetime of your steam generator iron. Your iron will remind you with light and sound when to perform cleaning. Only when your appliance is cold, simply open the Easy De-Calc knob, and collect the dirty water and scale in a cup.

OptimalTemp



One perfect setting for all your clothes. Always the perfect combination of steam & temperature because: 1) Advanced Smart Control Processor sets the perfect combination of steam & temperature 2) The ultra powerful cyclonic steam chamber delivers powerful constant steam for all your fabrics

Specifications

Fast & powerful crease removal

- Soleplate: SteamGlide
- OptimalTEMP technology
- Steam output
- Steam boost: 230 g
- Vertical steaming
- Pressure: Up to 5
- Steam tip
- Power: 2400 W

Easy to use

- Water tank capacity: 1500 ml
- Filling and emptying water: Detachable water tank, Extra large filling hole
- Refill any time
- Heat up time: 2 min
- Hose storage: Hose storage compartment
- Cord storage: Cord storage compartment
- Power cord length: 1.8 m
- Cord freedom (swivel): 180 degree cord freedom
- Hose length: 1.7 m
- Safe for all fabrics: Even for delicates like silks

Calc management

- Suitable for tap water
- Calc clean solution: Easy De-calc
- Calc clean reminder

Technical specifications

- Weight of iron: 1.2 kg
- Weight of iron + base: 5 kg



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

