

# PHILIPS

Steam generator  
iron

PerfectCare Expert

Up to 6.5 bar pressure

330 g steam boost

Carry lock

1.5L detachable water tank

GC9237/20



## Carefree ironing, no setting required

### Detachable water tank for easy filling

Iron any ironable garment from silk, to linen, to cotton, to cashmere...in any order, without having to adjust. Your Philips PerfectCare iron delivers fast results without risk of burn or shine for all your garments. Truly simple ironing.

#### **Carefree ironing, no temperature setting required**

- Iron from jeans to silk with no temperature setting required
- Safe to leave the hot soleplate on the ironing board

#### **Fast and powerful ironing**

- Ready to use in 2 minutes with unlimited refill
- 1.5 L detachable water tank, up to 2 hours of ironing
- Descale effectively and easily your appliance to prolong it
- Steam boost up to 300 g
- Our best gliding soleplate
- Up to 6 bar pressure



# Highlights

## Steam ready in 2 minutes



Steam is ready to use in 2min and can be refilled at anytime during ironing.

## 1.5 L detachable water tank

The watertank can be removed to be refilled easily under the tap. The large filling hole makes the refilling fast. Thanks to the 1.5 L watertank capacity, you can iron up to 2 hours continuously without any refills.

## Easy De-Calc



Ultra long lasting steam performance: Philips' exclusive Easy De-Calc function provides the ideal way to get rid of limescale and extend the lifetime of your steam generator iron. Your iron will remind you with light and sound when to perform cleaning. Only when your appliance is cold, simply open the Easy De-Calc knob, and collect the dirty water and scale in a cup.

## OptimalTEMP technology



Now you can iron from jeans to silk with no temperature setting required. Guaranteed no burn on all ironable fabrics. Revolutionary technology with the 1) Advanced Smart Control Processor which controls precisely the soleplate temperature. You do not need to adjust temperature 2) Powerful Cyclonic steam chamber which delivers powerful consistent steam, making ironing easier and faster.

## Safe rest



The Philips innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. During ironing, no need to put your iron back to the base station, just leave the hot iron soleplate directly on the garments or cotton ironing board cover without additional resting accessory. It will not damage any of your ironable garments, neither the board. This makes your ironing easier with less wrist efforts.

## Steam boost up to 300 g

The steam boost can be used for vertical steaming and tough creases.

## T-ionicGlide soleplate



Our best gliding and most scratch resistant, 5star rated soleplate with integrated Titanium-Oxide layer

## Up to 6 bar pressure

The more steam, the faster the ironing. Consistent powerful steam is generated which penetrates deep inside the garments making ironing faster and better. Steam power can be regulated to fit your needs.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Fast & powerful crease removal

Soleplate: SteamGlide  
OptimalTEMP technology  
Vertical steaming  
Pressure: Up to 6  
Steam tip  
Power: 2400 W  
Steam boost: 330 g  
Safe rest  
Steam output control  
Variable steam settings

## Easy to use

Water tank capacity: 1500 ml  
Filling and emptying water: Detachable water tank, Extra large filling hole  
Refill any time  
Heat up time: 2 min  
Hose storage: Hose storage compartment  
Cord storage: Cord storage compartment  
Cord freedom (swivel): 180 degree cord freedom  
Hose length: 1.7 m  
Safe for all fabrics: Even for delicates like silks  
Power cord length: 1.8 m

## Calc management

Suitable for tap water  
Calc clean solution: Easy De-calc  
Calc clean reminder

## Technical specifications

Packaging dimensions: 30.5 x 33.5 x 49.1 cm  
Product dimensions: 28.3 x 26.3 x 42.4 cm  
Weight of iron: 1.2 kg  
Weight of iron + base: 5 kg

