



Steam generator iron

- Max 6.7-bar pressure
- Up to 450 g steam boost
- 2.5-l water tank capacity
- Ultra-light iron

GC9405

Super-powerful ironing

with ultra-light iron

PerfectCare Aqua Pro comes with our ultra-light iron and extra-large 2.5-l water tank — ideal for long ironing sessions and perfect vertical steaming.

Benefits

No temperature setting needed; no burning, guaranteed

- Go from ironing jeans to silk; no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board
- Tested and approved by independent textile experts

Fast ironing with continuous powerful steam

- Easy and efficient descaling system
- Save energy with ECO mode
- Philips' best gliding and most scratch-resistant soleplate
- Powerful steam for ultimate crease removal

Ultimate ironing experience

- Extra-large water tank for longer continuous use
- Safe and secure carry lock
- Automatic switch-off for safety and energy saving
- Enjoy powerful ironing with minimum noise
- Lightweight and comfortable to handle

PHILIPS

Features

2.5-l water tank




The water tank has an extra-large 2.5-l capacity, so you get the convenience of up to 3 hours of continuous use with no need to top up the tank. It's also transparent, so you can get a 360° view of the tank to easily see how much water you have left to continue creating steam efficiently. When you do need to refill, your steam generator iron has a large filling hole that allows you to easily fill the water tank under the tap, or alternatively with a jug or bottle at any time during ironing.

Easy De-calc



Regular descaling protects your iron and ensures you'll continue to get the very best steam performance. The exclusively designed and ideally positioned Easy De-Calc Plus function provides the ideal way to get rid of limescale and extend the lifespan of your steam generator iron. The iron will remind you with both light and sound when it's time to clean and descale. Then when your appliance is cold, simply remove the Easy De-Calc knob, collect the dirty water and scale into a cup and discard.

Energy saving



ECO mode allows you to save energy without compromising your ironing results. The ECO mode uses a reduced amount of steam, but still a sufficient amount to iron all your garments.

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron all fabrics, from jeans to silk, with no burning guaranteed thanks to the perfect combination of temperature and continuous powerful steam.

Safe carry lock



Your steam generator iron includes a safe carry lock, which securely fastens your iron to its base without the risk of it slipping or someone touching the hot soleplate. It ensures safe and easy transportation around the house, to and from storage.

Safe rest



Innovative OptimalTEMP technology guarantees no burning on any ironable fabric. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

Safety auto off



The safety auto-off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind about safety.

Silent steam technology



Powerful steam doesn't have to mean noisy ironing. Enjoy ironing with family around, whilst watching TV or when listening to music, without being disturbed by the noise. The steam generator is fitted with silencing steam filters to minimise the noise of the steam and a sound-absorbing platform to reduce the noise of vibration in the base.

Tested and approved



This iron is tested and approved by independent textile expert institutes, such as DWI, IWTO and Woolmark, for its excellent ironing performance. The Woolmark Apparel Care programme helps consumers to identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips, with its exclusive OptimalTEMP technology, is so far

PerfectCare Aqua Pro

the only ironing brand to be certified with the Gold standard from Woolmark. You can be confident that our Woolmark-approved apparel care products are ideal for any wool garments.

T-ionicGlide soleplate



The T-ionic Glide is Philips' most premium soleplate, promising superior gliding for faster, effortless ironing. It has a stainless steel base which is harder and more durable than aluminium, with an integrated titanium oxide layer for advanced scratch resistance. Plus the carefully designed shape and vents provide even better steam distribution for faster crease removal.

Ultra-powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even tough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.

Ultra-lightweight iron



Your steam generator iron is amazingly light and comfortable to handle. It glides easily over your garments, removes the toughest creases in no time and reduces strain on your wrist. It also makes vertical steaming very easy and effective: you can now comfortably and effectively remove the creases in your delicate items, such as silk blouses, dresses and jackets, and even difficult-to-iron garments with pleats, decorations or buttons.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Technology

For all ironable fabrics	Yes
No burns	Yes
No temperature settings needed	Yes
OptimalTEMP technology	Yes
Silent steam technology	Yes
Cyclonic steam chamber	Yes
Smart Control Processor	Yes

Easy to use

Safe on all ironable fabrics	Even delicates like silk
Soleplate name	T-ionicGlide
Water tank capacity	2500 ml
Power cord length	1.8 m
Refill anytime during use	Yes
Safety auto off	Yes
Tap water suitable	Yes
Soleplate scratch resistance	5 stars
Cord freedom (swivel)	360 degree cord freedom
Extra-large filling hole	Yes
Heat-up time	2 min
Hose length	1.7 m
Precision steam tip	Yes
Ready to use	Light indicator
Soleplate gliding performance	5 stars

Scale management

Descaling and cleaning	Easy De-calc
Descaling reminder	Light Yes

Storage

Carry lock	For transportation and safety
Cord storage	Velcro fix
Hose storage	Hose storage compartment

Size and weight

Product dimensions (W x H x D)	36.2 x 27 x 26.3 cm
Weight of iron	0.8 kg
Weight of iron + base	4.2 kg

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

Product packaging	100% recyclable
User manual	100% recycled paper
Energy saving mode	Yes

Fast crease removal

Continuous steam	Up to 120 g/min
Power	Max 2100 W
Pressure	Max 6.7 bar
Ready to use	2 min

PerfectCare Aqua Pro

Steam boost	Up to 450 g
Steam-on-demand	Yes
Variable steam levels	Yes
Vertical steam	Yes
Voltage	220 - 240 V

Packaging dimensions

Height	30.20 cm
Width	41.50 cm
Depth	28.40 cm

Net weight	4.33 kg
Gross weight	5.51 kg
EAN	08710103789918
Number of products included	1
Country of origin	ID
Harmonised Systems Code	851640



data subject to change
2018, December 20

Version: 8.5.1
EAN: 08710103789918

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com