

PHILIPS

Steam generator
iron

PerfectCare Elite

Max. 7.5 bar pressure

Up to 520 g steam boost

1.8 l water tank capacity

Detachable water tank



GC9635/26



The most powerful steam for the fastest ironing* with ultra-light iron

PerfectCare Elite is Philips' best and most efficient steam generator iron. With OptimalTEMP technology, you can now iron everything from jeans to silk with no temperature setting needed. Guaranteed no burns on all ironable garments.

No temperature setting needed; no burning, guaranteed

- Go from ironing jeans to silk; no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- Easy and efficient descaling system
- Philips' best gliding and most scratch-resistant soleplate
- Save energy with ECO mode

Ultimate ironing experience

- Lightweight and comfortable to handle
- Large detachable water tank for easy refilling
- Safe and secure carry lock
- Automatic switch-off for safety and energy saving

Highlights

Ultra-powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even tough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron all fabrics, from jeans to silk, with no burning guaranteed thanks to the perfect combination of temperature and continuous powerful steam.

Safe rest



Innovative OptimalTEMP technology guarantees no burning on any ironable fabric. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps

to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

Ultra-lightweight iron



Your steam generator iron is amazingly light and comfortable to handle. It glides easily over your garments, removes the toughest creases in no time and reduces strain on your wrist. It also makes vertical steaming very easy and effective: you can now comfortably and effectively remove the creases in your delicate items, such as silk blouses, dresses and jackets, and even difficult-to-iron garments with pleats, decorations or buttons.

1.8 l detachable water tank



The detachable water tank allows you to easily refill anytime without stopping the appliance. It has a large filling hole so you can simply fill the water tank under the tap. It has a 1.8 l capacity, so you get the convenience of up to 2 hours of continuous use, with no need to top up the tank.

Easy De-Calc Plus



Regular descaling protects your iron and ensures you'll continue to get the very best steam performance. The exclusively designed

and ideally positioned Easy De-Calc Plus function provides the ideal way to get rid of limescale and extend the lifespan of your steam generator iron. The iron will remind you with both light and sound when it's time to clean and descale. Then when your appliance is cold, simply remove the Easy De-Calc knob, collect the dirty water and scale into a cup and discard.

T-ionicGlide soleplate



The T-ionic Glide is Philips' most premium soleplate, promising superior gliding for faster, effortless ironing. It has a stainless steel base which is harder and more durable than aluminium, with an integrated titanium oxide layer for advanced scratch resistance. Plus the carefully designed shape and vents provide even better steam distribution for faster crease removal.

Safety auto off



The safety auto-off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind about safety.

Specifications

Technology

Cyclonic steam chamber
For all ironable fabrics
No burns
No temperature settings needed
OptimalTEMP technology
Smart Control Processor

Fast crease removal

Continuous steam: Up to 155 g/min
Power: Max 2700 W
Pressure: Max. 7.5 bar
Ready to use: 2 min
Steam boost: Up to 520 g
Steam-on-demand
Variable steam levels
Vertical steam
Voltage: 220 – 240 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk
Soleplate gliding performance: 5 stars

Soleplate name: T-ionicGlide

Water tank capacity: 1800 ml
Detachable water tank
Extra-stable heel rest
Hose length: 1.7 m
Low water alert
Power cord length: 1.8 m
Precision steam tip
Ready to use: Light indicator, Sound indicator
Refill anytime during use
Safety auto off
Soleplate scratch resistance: 5 stars
Tap water suitable
Heat-up time: 2 min
Extra-large filling hole

Scale management

Descaling and cleaning: Easy De-calc Plus
Descaling reminder: Light, Yes

Storage

Carry lock: For transportation and safety
Cord storage: Cord storage compartment, Velcro fix
Hose storage: Hose storage compartment

Size and weight

Packaging dimensions (W x H x D): 31 x 35 x 51 cm
Product dimensions (W x H x D): 23.3 x 28.5 x 45.3 cm
Weight of iron: 0.8 kg
Weight of iron + base: 5.1 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
Product packaging: 100% recyclable
User manual: 100% recycled paper

