

# PHILIPS

Steam generator  
iron


PerfectCare Elite

Max. 7.5 bar pressure

Up to 520 g steam boost

1.8 l water tank capacity

Detachable water tank



GC9635/26



## The most powerful steam for the fastest ironing\* with ultra-light iron

PerfectCare Elite is Philips' best and most efficient steam generator iron. With OptimalTEMP technology, you can now iron everything from jeans to silk with no temperature setting needed. Guaranteed no burns on all ironable garments.

### **No temperature setting needed; no burning, guaranteed**

- Go from ironing jeans to silk; no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board
- Tested and approved by independent textile experts

### **Fast ironing with continuous powerful steam**

- Powerful steam for ultimate crease removal
- Easy and efficient descaling system
- Philips' best gliding and most scratch-resistant soleplate
- Save energy with ECO mode

### **Ultimate ironing experience**

- Lightweight and comfortable to handle
- Large detachable water tank for easy refilling
- Safe and secure carry lock
- Automatic switch-off for safety and energy saving

# Highlights

## Ultra-powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even tough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.

## OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron all fabrics, from jeans to silk, with no burning guaranteed thanks to the perfect combination of temperature and continuous powerful steam.


## Safe rest



Innovative OptimalTEMP technology guarantees no burning on any ironable fabric. As well as the reassurance this provides whilst

ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

## Tested and approved



This iron is tested and approved by independent textile expert institutes, such as DWI, IWTO and Woolmark, for its excellent ironing performance. The Woolmark Apparel Care programme helps consumers to identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips, with its exclusive OptimalTEMP technology, is so far the only ironing brand to be certified with the Gold standard from Woolmark. You can be confident that our Woolmark-approved apparel care products are ideal for any wool garments.

## Ultra-lightweight iron



Your steam generator iron is amazingly light and comfortable to handle. It glides easily over your garments, removes the toughest creases in no time and reduces strain on your wrist. It also makes vertical steaming very easy and effective: you can now comfortably and effectively remove the creases in your delicate

items, such as silk blouses, dresses and jackets, and even difficult-to-iron garments with pleats, decorations or buttons.

## 1.8 l detachable water tank



The detachable water tank allows you to easily refill anytime without stopping the appliance. It has a large filling hole so you can simply fill the water tank under the tap. It has a 1.8 l capacity, so you get the convenience of up to 2 hours of continuous use, with no need to top up the tank.

## Easy De-Calc Plus



Regular descaling protects your iron and ensures you'll continue to get the very best steam performance. The exclusively designed and ideally positioned Easy De-Calc Plus function provides the ideal way to get rid of limescale and extend the lifespan of your steam generator iron. The iron will remind you with both light and sound when it's time to clean and descale. Then when your appliance is cold, simply remove the Easy De-Calc knob, collect the dirty water and scale into a cup and discard.

# Specifications

## Technology

Cyclonic steam chamber  
For all ironable fabrics  
No burns  
No temperature settings needed  
OptimalTEMP technology  
Smart Control Processor

## Fast crease removal

Continuous steam: Up to 155 g/min  
Power: Max 2700 W  
Pressure: Max. 7.5 bar  
Ready to use: 2 min  
Steam boost: Up to 520 g  
Steam-on-demand  
Variable steam levels  
Vertical steam  
Voltage: 220 - 240 V

## Easy to use

Safe on all ironable fabrics: Even delicates like silk  
Soleplate gliding performance: 5 stars

Soleplate name: T-ionicGlide  
Water tank capacity: 1800 ml  
Detachable water tank  
Extra-stable heel rest  
Hose length: 1.7 m  
Low water alert  
Power cord length: 1.8 m  
Precision steam tip  
Ready to use: Light indicator, Sound indicator  
Refill anytime during use  
Safety auto off  
Soleplate scratch resistance: 5 stars  
Tap water suitable  
Heat-up time: 2 min  
Extra-large filling hole

## Scale management

Descaling and cleaning: Easy De-calc Plus  
Descaling reminder: Light, Yes

## Storage

Carry lock: For transportation and safety  
Cord storage: Cord storage compartment, Velcro fix  
Hose storage: Hose storage compartment

## Size and weight

Packaging dimensions (W x H x D): 31 x 35 x 51 cm  
Product dimensions (W x H x D): 23.3 x 28.5 x 45.3 cm  
Weight of iron: 0.8 kg  
Weight of iron + base: 5.1 kg

## Guarantee

2 year worldwide guarantee

## Green efficiency

Energy saving mode  
Product packaging: 100% recyclable  
User manual: 100% recycled paper

