



Steam generator iron

- Max. 7.5 bar pressure
- Up to 520 g steam boost
- 1.8 l water tank capacity
- Detachable water tank

GC9635/26

The most powerful steam for the fastest ironing*

with ultra-light iron

PerfectCare Elite is Philips' best and most efficient steam generator iron. With OptimalTEMP technology, you can now iron everything from jeans to silk with no temperature setting needed. Guaranteed no burns on all ironable garments.

Benefits

[No temperature setting needed; no burning, guaranteed](#)

- Go from ironing jeans to silk; no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board
- Tested and approved by independent textile experts

[Fast ironing with continuous powerful steam](#)

- Powerful steam for ultimate crease removal
- Easy and efficient descaling system
- Philips' best gliding and most scratch-resistant soleplate

- Save energy with ECO mode

[Ultimate ironing experience](#)

- Lightweight and comfortable to handle
- Large detachable water tank for easy refilling
- Automatic switch-off for safety and energy saving
- Safe and secure carry lock

PHILIPS


Features

Ultra-powerful steam



An ultra-fast ironing experience can be yours with revolutionary technology. The powerful and continuous steam tackles even tough creases, and thicker fabrics are smoothed out with ease and speed. Plus there's an extra steam boost if needed, perfect for vertical steaming or stubborn creases.

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron all fabrics, from jeans to silk, with no burning guaranteed thanks to the perfect combination of temperature and continuous powerful steam.

Safe rest



Innovative OptimalTEMP technology guarantees no burning on any ironable fabric. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

Tested and approved



This iron is tested and approved by independent textile expert institutes, such as DWI, IWTO and Woolmark, for its excellent ironing performance. The Woolmark Apparel Care programme helps consumers to identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips, with its exclusive OptimalTEMP technology, is so far the only ironing brand to be certified with the Gold standard from Woolmark. You can be confident that our Woolmark-approved apparel care products are ideal for any wool garments.

Ultra-lightweight iron



Your steam generator iron is amazingly light and comfortable to handle. It glides easily over your garments, removes the toughest creases in no time and reduces strain on your wrist. It also makes vertical steaming very easy and effective: you can now comfortably and effectively remove the creases in your delicate items, such as silk blouses, dresses and jackets, and even difficult-to-iron garments with pleats, decorations or buttons.

1.8 l detachable water tank



The detachable water tank allows you to easily refill anytime without stopping the appliance. It has a large filling hole so you can simply fill the water tank under the tap. It has a 1.8 l capacity, so you get the convenience of up to 2 hours of continuous use, with no need to top up the tank.

Easy De-Calc Plus



Regular descaling protects your iron and ensures you'll continue to get the very best steam performance. The exclusively designed and ideally positioned Easy De-Calc Plus function provides the ideal way to get rid of limescale and extend the lifespan of your steam generator iron. The iron will remind you with both light and sound when it's time to clean and descale. Then when your appliance is cold, simply remove the Easy De-Calc knob, collect the dirty water and scale into a cup and discard.

T-ionicGlide soleplate



The T-ionic Glide is Philips' most premium soleplate, promising superior gliding for faster, effortless ironing. It has a stainless steel base which is harder and more durable than aluminium, with an integrated titanium oxide layer for advanced scratch resistance. Plus the carefully designed shape and vents provide even better steam distribution for faster crease removal.


PerfectCare Elite

Safety auto off



The safety auto-off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind about safety.

Energy saving



ECO mode allows you to save energy without compromising your ironing results. The ECO mode uses a reduced amount of steam, but still a sufficient amount to iron all your garments.

Safe carry lock



Your steam generator iron includes a safe carry lock, which securely fastens your iron to its base without the risk of it slipping or someone touching the hot soleplate. It ensures safe and easy transportation around the house, to and from storage.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Technology

Cyclonic steam chamber	Yes
For all ironable fabrics	Yes
No burns	Yes
No temperature settings needed	Yes
OptimalTEMP technology	Yes
Smart Control Processor	Yes

Fast crease removal

Continuous steam Power	Up to 155 g/min Max 2700 W
Pressure	Max. 7.5 bar
Ready to use	2 min
Steam boost	Up to 520 g
Steam-on-demand	Yes
Variable steam levels	Yes
Vertical steam	Yes
Voltage	220 - 240 V

Easy to use

Safe on all ironable fabrics	Even delicates like silk
Soleplate gliding performance	5 stars
Soleplate name	T-ionicGlide
Water tank capacity	1800 ml
Detachable water tank	Yes
Extra-stable heel rest	Yes
Hose length	1.7 m
Low water alert	Yes
Power cord length	1.8 m
Precision steam tip	Yes
Ready to use	Light indicator Sound indicator
Refill anytime during use	Yes
Safety auto off	Yes

Soleplate scratch resistance	5 stars
Tap water suitable	Yes
Heat-up time	2 min
Extra-large filling hole	Yes

Scale management

Descaling and cleaning	Easy De-calc Plus
Descaling reminder	Light Yes

Storage

Carry lock	For transportation and safety
Cord storage	Cord storage compartment Velcro fix
Hose storage	Hose storage compartment

Size and weight

Packaging dimensions (W x H x D)	31 x 35 x 51 cm
Product dimensions (W x H x D)	23.3 x 28.5 x 45.3 cm
Weight of iron	0.8 kg
Weight of iron + base	5.1 kg

Guarantee

2 year worldwide guarantee	Yes
----------------------------	-----

Green efficiency

Energy saving mode	Yes
Product packaging	100% recyclable
User manual	100% recycled paper

Packaging dimensions

Height	35.00 cm
Width	31.00 cm
Depth	51.00 cm
Net weight	5.41 kg

PerfectCare Elite

Gross weight 7.33 kg
EAN 08710103875352
Number of products included 1
Country of origin ID
Harmonised Systems Code 851640

Width 31.00 cm
Height 35.00 cm
Gross weight 7.33 kg
EAN 18710103875359
Number of consumer packages 1

Outer Carton

Length 51.00 cm

* Iron weight & steam rate (norm IEC60311), vs. the 10 best-selling steam generators; tested Dec. 2014



data subject to change
2018, December 20
Version: 1.0.1
EAN: 08710103875352

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com