

PHILIPS

Steam generator
iron

PerfectCare Elite

Max 7.5 bar pressure

Up to 500 g steam boost

1.8 L water tank capacity

Detachable water tank



GC9650/80



Most powerful steam for the fastest ironing* with Ultra-light iron

PerfectCare Elite is the best and most efficient steam generator iron from Philips. With OptimalTEMP technology, you can now iron from jeans to silk with no temperature setting needed. Guaranteed no burns on all ironable garments.

No temperature setting needed, guaranteed no burn

- Iron jeans to silk, no need to change temperature setting
- Safe to leave the hot soleplate on the ironing board
- Tested and approved by independent textile experts

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- Easy and efficient descaling system
- Philips best gliding and most scratch resistant soleplate
- Save energy with ECO mode

Ultimate ironing experience

- Light weight and comfortable to handle
- Large detachable water tank for easy refilling
- Safe and secure carry lock
- Automatic switch off for safety and energy saving



asimpleswitch.com


Highlights

1.8 L detachable water tank




The detachable water tank allows you to easily refill anytime without stopping the appliance. It has a large filling hole so you can simply fill the water tank under the tap. It has a 1.8 L capacity, so you get the convenience of up to 2 hours of continuous use, with no need to top-up the tank.

Energy saving



ECO mode allows you to save energy without compromising your ironing results. The ECO mode uses a reduced amount of steam, but still a sufficient amount to iron all your garments.

OptimalTEMP technology



With OptimalTEMP technology you'll no longer have to waste time changing temperature settings, waiting for the temperature to adjust or pre-sorting clothes. Iron fabrics from jeans to silk, with guaranteed no burns thanks to the perfect combination of temperature and continuous powerful steam.

Safe carry lock



Your steam generator iron includes a safe carry lock which securely fastens your iron to its base without the risk of slipping or someone touching the hot soleplate. It ensures safe and easy transportation around the house, to and from storage.

Safe rest



Innovative OptimalTEMP technology guarantees no burn on all ironable fabrics. As well as the reassurance this provides whilst ironing, it also means you can leave the hot iron soleplate directly on your cotton ironing board without causing any damage. This helps to reduce any discomfort to your wrists, as you won't need to lift the iron to and from its base as often.

Safety auto off



The safety auto off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you safety peace of mind.

Tested and approved



This iron is tested and approved by independent textile expert institutes such as DWI, IWTO and Woolmark, for its excellent ironing performance. The Woolmark Apparel Care program helps consumers identify quality laundry products that are approved by The Woolmark Company for use on wool products. Philips with its exclusive OptimalTEMP technology is so far the only ironing brand able to be certified with the Gold standard from Woolmark. You can be confident that our Woolmark-approved apparel care products are ideally suited for any wool garments.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Easy to use

Detachable water tank
Extra large filling hole
Heat up time: 2 min
Hose length: 1.9 m
Low water alert
Power cord length: 2 m
Precision steam tip
Ready to use: Light indicator, Sound indicator
Refill any time during use
Safe on all ironable fabrics: Even delicates like silk
Safety auto off
Soleplate gliding performance: 5 stars
Soleplate name: T-ionicGlide
Soleplate scratch resistance: 5 stars
Tap water suitable
Water tank capacity: 1800 ml

Fast crease removal

Continuous steam: Up to 150 g/min
Power: Max 2400 W
Pressure: Max 7.5 bar

Ready to use: 2 min
Steam boost: Up to 500 g
Steam-on-demand
Variable steam levels
Vertical steam
Voltage: 220 - 240 V

Green efficiency

Energy saving mode
Product packaging: 100% recyclable
User manual: 100% recycled paper

Guarantee

2 year worldwide guarantee

Scale management

Descaling and cleaning: Easy De-calc Plus
Descaling reminder: Light, Yes

Size and weight

Packaging dimensions (WxHxL): 31 x 35 x 51 cm
Product dimensions (WxHxL): 23.3 x 28.5 x

45.3 cm
Weight of iron: 0.8 kg
Weight of iron + base: 5.1 kg

Storage

Carry lock: For transportation and safety
Cord storage: Cord storage compartment, Velcro fix
Hose storage: Hose storage compartment

Technology

Cyclonic steam chamber
For all ironable fabrics
No burns
No temperature settings needed
OptimalTEMP technology
Smart Control Processor
Silent steam Technology

Accessories included

Glove for extra protection

