

PHILIPS

Steam generator
iron

PerfectCare Elite
Plus

Up to 520g steam boost

1.8 L detachable water tank

OptimalTEMP Technology

Intelligent automatic steam



GC9660/36



The fastest, most powerful iron* just got smarter With intelligent automatic steam

PerfectCare Elite Plus is the most powerful and fastest steam generator in the world, with ultra-light iron and intelligent automatic steam for ultimate convenience. No temperature settings is required and no burns – guaranteed.

No temperature setting needed, guaranteed no burn

- OptimalTEMP technology, no temperature settings required
- No burns – guaranteed

Fast ironing with continuous powerful steam

- Powerful steam for ultimate crease removal
- Intelligent automatic steam for faster, easier ironing
- Easy and efficient descaling system for lasting performance
- T-ionicGlide soleplate, ultimate gliding & durability
- Save energy with ECO mode

Ultimate ironing experience

- Light weight and comfortable iron to handle
- Carry lock for safe and easy transport
- Automatic shut off when iron is left unattended
- Large detachable water tank for easy refilling



asimpleswitch.com

Highlights

No temperature setting needed



Iron everything from jeans to silk without adjusting the temperature. Thanks to OptimalTEMP, no dial or settings are needed. So there's no more pre-sorting the laundry, or waiting for the iron to heat up and cool down. You're ready for any fabric, anytime

No burns – guaranteed



Thanks to OptimalTEMP technology, we guarantee this iron will never cause burns to any ironable fabric. You can even leave it resting face down on your clothes or ironing board. No burns, no shine. Guaranteed.

Ultra-powerful steam



Strong, continuous steam tackles even the thickest fabrics with ease. Watch stubborn creases melt away with an extra steam boost just where you need it. This extra steam is perfect for vertical steaming to refresh clothes and curtains, too.

Intelligent automatic steam



Our DynamiQ smart sensor knows exactly when and how the iron is moving, delivering powerful steam where you need it most – for easier ironing and faster results.

Ultra-light weight iron



The iron is amazingly light and comfortable to handle, gliding easily and reducing wrist strain. Its minimal weight also makes it easy and effective for vertical steaming of curtains and hanging clothes.

T-ionicGlide soleplate




T-ionicGlide is our best soleplate for ultimate gliding performance and maximum scratch resistance. Its stainless steel base is twice as hard as a regular aluminum base, and our patented 6-layer coating with advanced titanium layer glides effortlessly for the fastest results.

Easy De-Calc Plus



Regular descaling protects your iron, extends its lifetime, and ensures the best steam performance. Our exclusive Easy De-Calc Plus system collects limescale continuously with an indicator light and audio signal to tell you when it needs emptying. Simply remove the plug and let the water and scale particles flow out.

Auto shut off



The automatic shut off function automatically switches off your steam generator iron if it has not been used for a few minutes. This saves energy and gives you peace of mind.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technology

Auto steam sensor
Cyclonic steam chamber
For all ironable fabrics
No burns
No temperature settings needed
OptimalTEMP technology
Smart Control Processor
DynamiQ

Fast crease removal

Continuous steam: Up to 155 g/min
Power: Max 2700 W
Pressure: Max 7.5 bar
Ready to use: 2 min
Steam boost: Up to 520 g
Steam-on-demand
Vertical steam
Voltage: 220-240 V

Easy to use

Safe on all ironable fabrics: Even delicates like silk
Soleplate gliding performance: 5 stars
Soleplate name: T-ionicGlide
Water tank capacity: 1800 ml
Detachable water tank
Hose length: 1.7 m
Low water alert
Power cord length: 1.8 m
Precision steam tip
Ready to use: Sound indicator
Refill any time during use
Safety auto off
Soleplate scratch resistance: 5 stars
Tap water suitable

Scale management

Descaling and cleaning: Easy De-calc Plus
Descaling reminder: Light

Storage

Carry lock: For transportation and safety
Hose storage: Hose storage compartment

Size and weight

Packaging dimensions (WxHxL): 31 x 35 x 51 cm
Product dimensions (WxHxL): 23.3 x 28.5 x 45.3 cm
Total weight with packaging: 7.3 kg
Weight of iron: 0.8 kg
Weight of iron + base: 5.1 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
Energy saving*: 50 %
Product packaging: 100% recycable
User manual: 100% recycled paper

