

# PHILIPS

## Wardrobecare

GC9920



## Breathes new life into your clothes

### Integrated iron, steamer and refresher

The Wardrobe Care solution from Philips is a unique combination of an iron, a steamer and a refresher with an innovative ironing board. It helps you keep your and your family's clothes in beautiful shape and saves you time and money as well!

#### **The ultimate ironing experience**

- High-pressure steam iron
- Large heated board with NeverBurn cover
- Blowing setting prevents pressing marks
- Suction setting keeps fabric in place to avoid false creases

#### **Crease-free shirts quickly and easily**

- Unique board with one end especially for shirts

#### **Keeps your delicate garments in perfect shape**

- High-pressure steamer and vertical board

#### **Refreshes jackets and sweaters; less dry-cleaning**

- Auto-refresh mode creates a breeze to air your garments

#### **Hassle-free scale removal**

- Removes calc from your system automatically

# Highlights

## High-pressure steam iron



High-pressure steam iron makes sure the steam goes deep into your garment for optimal and faster crease removal.

## Large heated board with NeverBurn cover

The large heated board enables easier and more convenient ironing. The NeverBurn board cover is heat resistant, so you can rest your hot soleplate on the cover without the risk of burning or scorching. It also eliminates the inconvenience of having to repeatedly stressing your wrist to put the iron on its heel.

## Shirt-shaped board



One end of the board is specially designed for ironing shirts quickly and easily.

## High-pressure steamer



The powerful steamer and vertical board mean you can remove creases from delicate fabrics without the risk of damaging them.

## Refresher



Heated air from the board freshens your garments and reduces the need for dry-cleaning.

## Auto Calc-Clean function



The Auto Calc-Clean function automatically cleans your ironing system from calc. A 2-minute scale removal cycle is activated automatically when it is time to clean your system. All you have to do is empty the detachable rinse tank. It keeps your system as new and powerful as the day you bought it.

# Specifications

## Comfortable ironing

**Additional comfort:** Assisted height adjustment, Standing or sitting ironing  
**Anti-scale management:** Auto Calc-Clean function

**Safe in use:** Automatic shut-off when iron is left unattended

**Suitable for tap water**

**Water tank capacity:** 2500 ml

## Crease removal

**Continuous steam**

**Pressurised Steam:** Up to 4.5 bar

**Reaching tricky areas:** Pointed tip

## Easy to use

**Control:** Blowing setting, Condensation management, Indicator to empty rinse tank, Suction setting, Temperature ready light, Water

tank empty light

**Easy to set up and store:** Automatic cord winder, Easy storage compartments, Handle and wheels

**Ergonomics:** Lightweight iron and steamer

**Reaching tricky areas:** Steam tip

**Safe in use:** Safety shut-off

**Water tank:** Crystal clear, Detachable

## Service

2-year guarantee

## Technical specifications

**Frequency:** 50-60

**Power:** 2400

**Voltage:** 220 - 240

## Weight and dimensions

**Product weight:** 20

