




Philips GoPure Compact  
50  
Car air purifier

### Compact

Fine particles CADR\*:12m<sup>3</sup>/hour  
Air cleaning efficiency: 13min



GPC05BLKX1

## Healthy air in your car

Efficiently removes fine particles

Philips high-efficiency filtration technology removes fine particles like PM<sub>2.5</sub> with a Clean Air Delivery Rate (CADR) of 12m<sup>3</sup>/hour, to keep you and your family in good health.

#### Powerful air filtration

- Cleans your car air in just 13 min
- Fast removal of fine particles with CADR at 12m<sup>3</sup>/hour

#### Simplicity

- Automatic switch on
- Including 2m 12V power cable and mounting accessories

# PHILIPS

## Car air purifier

Compact Fine particles CADR\*:12m3/hour, Air cleaning efficiency: 13min

# Specifications

### Product description

- Designation: GoPure Compact 50
- Color: Black
- Noise level: 55 (one speed) dB
- Air particle sensor: No
- Automatic On/Off
- Filter replacement indicator: No
- Fragrance dispenser: No
- Frequency: 50 Hz
- Speed settings: No
- Power: 2.3 W
- Voltage: 12 V
- Filter Lifetime: 350 hr
- App enabled: No
- Air quality indicator (AQI): No
- Technology: Car air purifier

### Performance

- Air Cleaning Efficiency: 13 min
- Boost mode: No
- Fine particles filtration: CADR of 12m3/hour

### Replacement

- Filter type: GSF120X110X1
- GoPure clean air system type: GPSA30GPX1,

GPSA33GPX1, GPLS23GPX1

### Weight and dimensions

- Box dimensions (L x W x H): 50 x 50 x 80 mm
- Product dimensions (L x W x H): 17 x 30 x 40 mm
- Product weight: 500 g
- Box weight (incl. product): 670 g

### Marketing specifications

- Expected benefits: Healthy air in your car
- Product highlight: Compact

### Accessories in the box

- Mounting accessories: Attachment belt
- power cable length: 2 m


### Logistic data

- Quantity in box: 1
- Reference (Order entry): GPC05BLKX1
- Ordering code: 17404128
- EAN (APR): 8719018010087
- EAN (China): 6947939174041

GPC05BLKX1

# Highlights

### Particles filtration



Philips high efficiency particulate filtration removes fine particles found in car indoor environment with a Clean Air Delivery Rate (CADR) of 12m3/hour(50% of 0,3µm particles filtration; 3m3 chamber).This includes cigarette smoke, pollens, dust, PM2.5, and airborne virus or bacteria superior to 0,3 micron

### Clean air efficiency



Your Philips GoPure car air purifier will clean 50% of all fine particles inside your car in just 13 min. This has been tested in a 3m3 chamber, a volume similar to the interior of an average sedan car.

### Easy operation



Automatic switch on when you start your car

### Easy installation



Including 2m 12V power cable and mounting accessories for safe installation on armrest, headrest and under seats



Issue date 2018-06-19

Version: 6.0.1

12 NC: 9285 999 07801

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)