

PHILIPS

Automotive clean
air system

GoPure Compact

GP Compact 200

With healthy air indicator



GPC20GPX1



For fresh and clean air in your car

Enjoy fresh and clean air in your car with Philips GoPure Automotive Clean Air system. The Philips unique 3-stage filtration process removes up to 99% of in-car air pollution to keep you and your family in good health.

High air purification power

- Removes up to 99% of fine particles & toxic gasses.

Neutralises unpleasant odors

- 3x better than ionizer

Healthy air indicator

- 3 air-quality level indication

Easy operation

- Automatic switch on/off, filter replacement indicator

Highlights

Neutralizes unpleasant odors



HESA unique technology eliminates up to 99% of toxic gases and chemical pollutants: Interior plastics, car's upholstery 3x better tobacco smoke residue (nicotine) removal than ionizers: TUV Germany test based on DIN ISO/IEC 28360:2009-11 & DIN EN ISO 16000-9, calculated for 10 substances in 1M3 chamber

Healthy air indicator



Integrated air-particles sensor indicates current air quality: excellent (blue), fair (yellow), and poor (red)

Easy operation



The GP Compact 200 features an automatic switch-on when you start the car, 3 speed settings to adjust filtration power and a filter LED warning to indicate that filter needs to be changed (the filter lasts 8 - 12 months, according to car usage).

High air purification power



Thanks to the unique Philips GoPure technology combining HEPA and HESA filters, you can now enjoy pure air in your car. The 3-stage filtration process eliminates 99% of 0.3µm (PM2.5) harmful fine particles (incl. industry and exhaust fumes, dust, allergens, bacteria and viruses), and neutralizes 99% of toxic gaseous chemicals (incl. car interior plastics and upholstery)

Specifications

Product description

Technology: Car air purifier
Designation: GP Compact 200
Color: Grey Dark
Noise level: 40 (Low) - 50 (High) dB
Air particle sensor
Air quality indicator (AQI): 3 levels AQI
Automatic On/Off
Filter replacement indicator
Filter type: FIL301ACA
Fragrance dispenser: No
Frequency: 50 Hz
Speed settings: 2 speeds
Power: 3 W
Voltage: 12 V
Filter Lifetime: 350 hr
Clean Air Delivery Rate: 10 m³/h

Accessories included

Mounting accessories: Attachment belt suction cup, anti-slide pads
12v power cable length: 4m

Marketing specifications

Product highlight: Localizer
Expected benefits: Localizer

