

Philips GoPure Compact  
Automotive clean air  
system

**GP Compact 200**  
With healthy air indicator



**GPC20GPX1**



## For fresh and clean air in your car

Enjoy fresh and clean air in your car with Philips GoPure Automotive Clean Air system. The Philips unique 3-stage filtration process removes up to 99% of in-car air pollution to keep you and your family in good health.

### **High air purification power**

- Removes up to 99% of fine particles & toxic gasses.

### **Neutralises unpleasant odors**

- 3x better than ionizer

### **Healthy air indicator**

- 3 air-quality level indication

### **Easy operation**

- Automatic switch on/off, filter replacement indicator

# PHILIPS

# Highlights

## Neutralizes unpleasant odors



HESA unique technology eliminates up to 99% of toxic gases and chemical pollutants: Interior plastics, car's upholstery. 3x better tobacco smoke residue (nicotine) removal than ionizers: TUV Germany test based on DIN ISO/IEC 28360:2009-11 & DIN EN ISO 16000-9, calculated for 10 substances in 1M3 chamber

## Healthy air indicator



Integrated air-particles sensor indicates current air quality: excellent (blue), fair (yellow), and poor (red)

## Easy operation



The GP Compact 200 features an automatic switch-on when you start the car, 3 speed settings to adjust filtration power and a filter LED warning to indicate that filter needs to be changed (the filter lasts 8 - 12 months, according to car usage).

## High air purification power



Thanks to the unique Philips GoPure technology combining HEPA and HESA filters, you can now enjoy pure air in your car. The 3-stage filtration process eliminates 99% of 0.3µm (PM2.5) harmful fine particles (incl. industry and exhaust fumes, dust, allergens, bacteria and viruses), and neutralizes 99% of toxic gaseous chemicals (incl. car interior plastics and upholstery)

# Specifications

## Product description

- Technology: Automotive clean air system
- Designation: GP Compact 200
- Color: Grey Dark
- Noise level: 40 (Low) - 50 (High) dB
- Air particle sensor
- Air quality indicator (AQI): 3 levels AQI
- Automatic On/Off
- Filter replacement indicator
- Filter type: FIL301ACA
- Fragrance dispenser: No
- Frequency: 50 Hz
- Speed settings: 2 speeds
- Power: 3 W
- Voltage: 12 V
- Filter Lifetime: 350 hr
- Clean Air Delivery Rate: 10 m<sup>3</sup>/h

## Accessories included

- Mounting accessories: Attachment belt suction cup, anti-slide pads
- 12v power cable length: 4m

## Marketing specifications

- Product highlight: Localizer
- Expected benefits: Localizer



Issue date 2018-03-23

Version: 13.0.2

12 NC: 8670 001 17451

© 2018 Philips Lighting Holding B.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

[www.philips.com](http://www.philips.com)