



Philips GoPure SlimLine
230
Car air purifier

Air quality indicator

Fine particles CADR*:10m³/hour
Toxic gases CADR*: 10m³/hour
Air cleaning efficiency: 13min



GPSL23GPX1

Fresh and healthy air in your car

Efficiently removes fine particles and toxic gases

Philips unique high-efficiency filtration technology removes fine particles like PM_{2.5} with a Clean Air Delivery Rate (CADR) of 10m³/hour, and toxic gases with a CADR of 10m³/hour, to keep you and your family in good health.

Powerful air filtration

- Efficiently removes fine particles and toxic gases
- Cleans your car air in just 13 min

Refresh your air

- Refreshes your air with natural fragrance

Simplicity

- Automatic operations and filtration control
- Air quality Indicator
- Filter replacement indication
- Perfect in-car integration with installation in cup-holder

PHILIPS

Car air purifier

Air quality indicator Fine particles CADR*:10m³/hour, Toxic gases CADR*: 10m³/hour, Air cleaning efficiency: 13min

Highlights

Pollution filtration

Philips unique high-efficiency filtration technology removes fine particles like PM_{2.5} with a Clean Air Delivery Rate (CADR) of 10m³/hour, and toxic gases with a CADR of 10m³/hour, to keep you and your family in good health.

Clean air efficiency



Boost-mode filtration cleans air quickly at highest speed

Natural fragrance dispenser



GoPure refreshes your air with natural fragrance dispensing function. 1 fragrance cartridge included

Automatic filtration




Focus on driving, thanks to automatic operations and filtration control

Air quality Indicator



Integrated air-particles sensor indicates current air quality: excellent (blue), fair (yellow), and poor (red)

Filter replacement indication



Filter replacement indication when filter needs to be changed

Easy installation



Including 4m 12V power cable and cup-holder installation accessory, for perfect in-car integration

GPSL23GPX1

Specifications

Product description

- Air flow: 9.7 m³/h
- Noise level: 40 (Low) - 50 (Mid) - 55 (High) dB
- Air particle sensor
- Air quality indicator (AQI)
- Automatic On/Off
- Filter replacement indicator
- Fragrance dispenser
- Frequency: 50 Hz
- Speed settings: 3 speeds
- Power: 7 W
- Voltage: 12 V
- Filter Lifetime: 350 hr
- Technology: Car air purifier
- Color: Dark Grey
- Designation: GoPure Slimline 230
- App enabled: No

Performance

- Air Cleaning Efficiency: 13 min
- Filtration bacteria/virus: 70 %
- Boost mode
- Fine particles filtration: CADR of 10m³/hour
- Toxic gases & TVOC filtration: CADR of 10m³/hour

Marketing specifications

- Expected benefits: fresh healthy air in your car
- Product highlight: AQI, boost-mode, fragrance dispenser

Accessories in the box

- Mounting accessories: Cup-holder kit
- power cable length: 4 m
- Other mounting accessories: Attachment belt

Replacement

- Fragrance cartridge: 51200X3, 51201X3, 51202X3
- Filter type: GSF80X80X1

Weight and dimensions

- Box dimensions (L x W x H): 295 x 245 x 80 mm
- Product dimensions (L x W x H): 170 x 100 x 70 mm
- Product weight: 800 g
- Box weight (incl. product): 1200 g

Logistic data

- EAN (China): 6947939174003
- Ordering code (China): 17400328
- Quantity in box: 1
- Reference (Order entry): GPSL23GPX1



Issue date 2018-03-23

Version: 5.0.1

12 NC: 9285 999 07601

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com