



Philips GoSure Full HD
rear camera
ADR820 compatible

Crystal-clear rear recording
Upgrade your dash cam



GRC20XM

Your reliable witness on the road

Automatically capture your journey in vivid detail

The Philips GoSure ADR820 dash cam captures everything that happens on the road, in case of the unexpected. With this Full HD rear camera module to record from the back of your car too, you will have full coverage of your journey.

Full HD rear camera to upgrade your dash cam

- Upgrade your dash cam with a Full HD rear camera

Easy to install

- Plug-and-play Full HD rear camera

PHILIPS

ADR820 compatible
Crystal-clear rear recording Upgrade your dash cam

Specifications

Product description

- Designation: RC20 GRC20
- Technology: Automotive Driving Recorder
- Fixed Lens: 6-layer glass lens, FOV 110
- Video resolution: 1080p @ 20 fps
- Aperture Range: F/2.0
- Operating Temperature: -10°C to 60°C
- Storage Temperature: -20°C to 70°C
- Image Sensor: 2.0 megapixels

Weight and dimensions

- Product weight (g): 370
- Box weight (incl. product) (g): 490
- Height (cm): 6.5
- Length (cm): 16.5
- Width (cm): 10.3

Marketing specifications

- Expected benefits: Your driving safety guardian
- Product highlight: FHD & Optional GPS module

Logistic data

- Quantity in box: 1
- Reference: GRC20XM
- EAN1: 8727900340426
- EAN3: 8727900340433
- Ordering code: 34042630

Ordering information

- Order entry: GRC20XM
- Ordering code: 34042630

GRC20XM

Highlights

Upgrade your dash cam

With the Philips GoSure ADR820, you are fully protected on the road from the front. But how about the back of your car? Upgrade your dash cam with a Full HD camera module and enjoy your safe drive with crystal-clear recordings of what happens both in front of and behind your car.

Plug-and-play FHD rear camera

Don't worry about the installation of your Full HD rear camera module. It's easy. Simply fix the Full HD rear camera onto your rear window with the strong 3M tape, and plug it into your ADR820 with the cable provided. Now your car will be equipped with sharp eyes at the front and the back.



Issue date 2018-06-10

Version: 2.1.1

12 NC: 8670 001 53924

© 2018 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com