

# Suncare range 2002




HB 812      HB 851      HB 861      HB 971      HB 975

## HP FULLBODY: SUNMOBILE

	HB 812	HB 851	HB 861	HB 971	HB 975
<b>Features</b>					
Tanning field (cm)	190 x 70	190 x 70	190 x 70	190 x 70	190 x 70
Wattage (W) Tanning	1300	1750	1750	2200	2100
Relaxation					2530
HP lamps	3	4	4	4	4
Facial plus	-	-	-	●	-
Remote control	-	●	●	●	●
Foldable	●	●	●	●	●
Body - lamp distance (cm)	65	70	70	65	65

## Logistic data

<i>Dimensions (mm) (l x w x h)</i>					
- product	1090 x 490 x 450	760 x 515 x 265	760 x 515 x 265	890 x 620 x 320	890 x 620 x 320
- packaging	1210 x 490 x 450	900 x 640 x 255	900 x 640 x 255	970 x 700 x 400	970 x 700 x 400
Weight (kg)	± 29,8	± 35	± 35	± 41	± 45
Pallet quantity	8	12	12	6	6



HB 578      HB 579      HB 580      HB 581

## TL FULLBODY: SUNSTUDIO

	HB 578	HB 579	HB 580	HB 581
<b>Features</b>				
Tanning field (cm)	185 x 80	185 x 80	185 x 80	185 x 80
Side tanning (%)	80	80	80	80
Cleo Perf. S tubes	24	24	28	30
Facial	3 x PLL 36 W	1 x HPA 400 W	2 x HPA 400 W	3 x HPA 400 W
Fans	7	7	9	9
Wattage (W)	3050	3140	3850	4250
Remote control	●	●	●	●

## Logistic data

<i>Dimensions (mm) (l x w x h)</i>				
- Product	2080 x 980 x 9150	2080 x 980 x 9150	2080 x 980 x 9150	2080 x 980 x 9150
- Packaging Canopy	2300 x 1280 x 6180	2300 x 1280 x 6180	2300 x 1280 x 6180	2300 x 1280 x 6180
- Couch	2300 x 1280 x 4680	2300 x 1280 x 4680	2300 x 1280 x 4680	2300 x 1280 x 4680
- Ballast Box	-	-	943 x 688 x 281	943 x 688 x 281
Weight (kg)	186	189	222	229
Pallet quantity	1	1	1	1

\*TL facial



**PHILIPS**

*Let's make things better.*



HB 554

HB 555

HB 556



HB 557

HB 558



HB 172



HB 175



HB 181



HB 311



HB 406



HP 3614



HP 3616

## TL FULLBODY: STANDARD

HB 554

HB 555

HB 556

HB 557

HB 558

## Features

Tanning field (cm)	180 x 75	180 x 75	180 x 75	180 x 75	180 x 75
Wattage (W)	935	1160	1415	2300	2540
Vertical storage	●	●	●	-	-
Lamps (Cleo perf. S) 100 W	8	10	10	20	20
Facial HPA 400 W	-	-	●	-	●
Fans	1	1	1	2	2
Acrylic sheet	●	●	●	●	●
Height adjustment	●	●	●	-	-

## Logistic data

<i>Dimensions (mm) (l x w x h)</i>					
-product				1900 x 900 x 890	1900 x 900 x 890
Lamps vert.	1900 x 850 x 650	1900 x 850 x 650	1900 x 850 x 650		
Lamps horr.	1100 x 1870 x 850	1100 x 1870 x 850	1100 x 1870 x 850		
-Packaging	2110 x 1070 x 360	2110 x 1070 x 360	2110 x 1070 x 360	2110 x 1070 x 720	2110 x 1070 x 720
Weight (kg)	47	49	54	109	114
Pallet quantity	5	5	5	2	2

## HALFBODY/FACIALS

HB 172

HB 175

HB 181

HB 311

HB 406

## Features

Tanning field	21 x 27	21 x 27	21 x 27	30 x 40	40 x 60
Wattage (W)	75	75	105	140	440
Lamps	4 x Cleo 15 W	4 x Cleo 15 W	6 x Cleo 15 W	6 x Cleo 20 W	1 x HPA
Fans	-	-	-	-	●
Timer	●	●	●	●	●
Memomatics	-	●	●	●	●
Stand	-	-	-	○	○
Cord storage	-	-	-	●	●
Variable positioning	●	●			

## Logistic data

<i>Dimensions (mm) (l x w x h)</i>					
- Product	180 x 272 x 380	180 x 272 x 380	170 x 150 x 390	530 x 230 x 35	470 x 260 x 200
- Packaging	213 x 280 x 428	213 x 280 x 428	308 x 185 x 420	400 x 280 x 618	570 x 350 x 280
- Export	296 x 320 x 454	296 x 320 x 454	380 x 320 x 438	630 x 420 x 415	
Weight (kg)	2,9	2,9	3,8	5	6,6
Pallet quantity	64	64	72	40	36
Quantity of A-box	2	2	2	2	2

## INFRAPHIL

HP 3614

HP 3616

## Features

Wattage (W)	100	150
Cord storage	●	●
On-off switch	-	●
Prismatic	-	●
Variable positioning	●	●

## Logistic data

<i>Dimensions (mm) (l x w x h)</i>		
- Product	200 x 120 x 160	220 x 130 x 185
- Packaging	193 x 130 x 210	207 x 140 x 225
- Export	594 x 258 x 225	630 x 295 x 242
Weight (gr)	470	980
Quantity of A-box	6	6

● = standard  
○ = optional  
- = not available