

# PHILIPS

## Hair clipper

### Hairclipper series 3000

Stainless steel blades

13 length settings

45mins cordless use/8h charge

Incl. beard comb



HC3518/15



## Easy, even haircut

### Faster clipping without clogging\*

Get an easy haircut, quick and easily. DualCut technology with self-sharpening blades clips twice as fast\*. Trim-n-Flow technology features a comb designed to prevent clogging - so you can finish your style in one go.

#### Performance

- Trim-n-Flow technology for continuous cutting
- Maximum precision with double blades
- Get a perfect but protective trim

#### Precise length control

- Adjusts to different length settings
- Tames beards and stubble

#### Easy to use


- 45 minutes of cordless use after an 8-hour charge
- Ergonomic design for comfort and control
- Quick release blades for easy cleaning

#### Built to last

- The blades never need oiling
- Warranty for purchase protection

# Highlights

## Trim-n-Flow technology



Our Philips hair clipper with new, innovative comb is designed to prevent hair from getting stuck. So you can cut your hair, from start to finish, without interruptions.

## DualCut Technology



The Philips Hairclipper 3000 features advanced DualCut Technology for maximum precision. It comes with double blades, and is designed to stay as sharp as day 1.

## Stainless steel blades



The self-sharpening steel blades are designed to be incredibly long-lasting. Even after 5 years they cut with the same precision and accuracy as day 1.

## 13 lock-in length settings



Cut your hair to the exact length you want. Just select one of 12 length settings between 1mm to 23mm at 2mm increments, or remove the comb for a close 0.5mm trim.

## Cordless & corded use



Use the clipper cordless for maximum power and freedom. Its powerful NiMH battery which provides up to 45 minutes of cordless power after 8 hour of charging.

## Comfortable grip



Philips clippers have a textured grip designed for easy handling, so you can cut your hair with control and in comfort.

## Extra adjustable beard comb



Electric hair clippers to easily trim your beard or stubble, the adjustable beard comb has 12 length settings between 1mm to 23mm at 2mm increments, or you can remove the comb entirely for a close 0.5mm trim.

## Easy to clean



Clean your electric hair clippers with ease. Simply click open the head to release and clean the blades.

## Zero maintenance



Clipping power that's easy to maintain—our blades never need oiling.

# Specifications

## Cutting system

Trim-n-Flow technology

Cutter width: 41mm

Cutting element: Stainless steel blades

Number of length settings: 13

Precision (size of steps): By 2mm

Range of length settings: From 0.5 to 23 mm

## Accessories

**Comb:** Adjustable hair comb, Extra adjustable beard comb

**Maintenance:** Cleaning brush

## Ease of use

**Cleaning:** Removable cutter, Washable blades

**Operation:** Corded & Cordless use

**Maintenance free:** No oil needed

## Power

**Run time:** 45 minutes

**Charging:** 8 hours full charge

**Battery type:** Ni-MH

**Automatic voltage:** 100-240 V

## Design

**Handle:** Ergonomic grip & handling

## Service

2-year worldwide guarantee

