

# PHILIPS

## Hair clipper

### Hairclipper series 3000

Stainless steel blades

13 length settings

45mins cordless use/8h charge

Incl. beard comb



HC3518/15



## Easy, even haircut

### Faster clipping without clogging\*

Get an easy haircut, quick and easily. DualCut technology with self-sharpening blades clips twice as fast\*. Trim-n-Flow technology features a comb designed to prevent clogging - so you can finish your style in one go.

#### Performance

- Trim-n-Flow technology for continuous cutting
- Double-sharpened blades for 2 times faster clipping
- Self-sharpening stainless steel blades

#### Precise length control

- Easily select and lock-in 13 length settings: 0,5 to 23mm
- Includes a beard comb for 12 adjustable lengths: 1 to 23mm

#### Easy to use

- 45 minutes of cordless use after an 8-hour charge
- Ergonomic handle for more comfort and control
- Quick release blades for easy cleaning

#### Built to last

- Zero maintenance, no oil needed
- 2-year guarantee

# Highlights

## Trim-n-Flow technology



Our new, innovative comb is designed to prevent hair from getting stuck in the clipper. So you can continue cutting your hair, from start to finish, without interruption.

## DualCut Technology



Power through any type of hair with our advanced DualCut technology: an innovative two-sided cutting element that cuts hair twice as fast as one-sided blades.

## Stainless steel blades



Self-sharpening stainless steel blades are incredibly long-lasting. Even after 5 years, they cut just like they did on day one.

## 13 lock-in length settings



Simply select and lock in the length you want. The adjustable comb has 12 lock-in length settings from 1mm to 23mm, with precisely 2mm between each length. Remove the comb entirely for a close 0.5mm trim.

## Cordless & corded use



Use the clipper cordless for maximum power and freedom. Its powerful NiMH battery which provides up to 45 minutes of cordless power after 8 hour of charging.

## Comfortable grip



The HAIRCLIPPER Series 3000 is designed to be comfortable to use, convenient to handle and easy to operate. The special texture and grip allow you to easily move the clipper and cut all around your head.

## Extra adjustable beard comb



Whether you have a beard or want the perfect stubble, just attach the adjustable beard comb and select one of 12 lock-in settings, from 1 to 23mm. There are precisely 2mm between each length. To get a shorter stubble, remove the comb entirely for a close 0.5mm trim.

## Easy to clean



Simply click to release the detachable head to quickly release and clean the blades.

## Zero maintenance



No oil needed, for easy maintenance and to save you time.

# Specifications

## Cutting system

Trim-n-Flow technology

Cutter width: 41mm

Cutting element: Stainless steel blades

Number of length settings: 13

Precision (size of steps): By 2mm

Range of length settings: From 0.5 to 23 mm

## Accessories

**Comb:** Adjustable hair comb, Extra adjustable beard comb

**Maintenance:** Cleaning brush

## Ease of use

**Cleaning:** Removable cutter, Washable blades

**Operation:** Corded & Cordless use

**Maintenance free:** No oil needed

## Power

**Run time:** 45 minutes

**Charging:** 8 hours full charge

**Battery type:** Ni-MH

**Automatic voltage:** 100-240 V

## Design

**Handle:** Ergonomic grip & handling

## Service

2-year worldwide guarantee

