

PHILIPS

Hair clipper

Hairclipper series 3000

Stainless steel blades

13 length settings

75mins cordless use/8h charge

Incl. beard comb



HC3530/13



Easy, even haircut

Faster clipping without clogging*

Get an easy haircut, quick and easily. DualCut technology with self-sharpening blades clips twice as fast*. Trim-n-Flow technology features a comb designed to prevent clogging – so you can finish your style in one go.

Performance

- Trim-n-Flow technology for continuous cutting
- Double-sharpened blades for 2 times faster clipping
- Self-sharpening stainless steel blades

Precise length control

- Easily select and lock-in 13 length settings: 0,5 to 23mm
- Includes a beard comb for 12 adjustable lengths: 1 to 23mm

Easy to use

- 75 minutes of cordless use after an 8-hour charge
- Ergonomic handle for more comfort and control
- Quick release blades for easy cleaning

Built to last

- Zero maintenance, no oil needed
- 2-year guarantee



asimpleswitch.com

Highlights

Trim-n-Flow technology



Our new, innovative comb is designed to prevent hair from getting stuck in the clipper. So you can continue cutting your hair, from start to finish, without interruption.

DualCut Technology




Power through any type of hair with our advanced DualCut technology: an innovative two-sided cutting element that cuts hair twice as fast as one-sided blades.

Stainless steel blades



Self-sharpening stainless steel blades are incredibly long-lasting. Even after 5 years, they cut just like they did on day one.

13 lock-in length settings



Simply select and lock in the length you want. The adjustable comb has 12 lock-in length settings from 1mm to 23mm, with precisely 2mm between each length. Remove the comb entirely for a close 0.5mm trim.

Cordless & corded use



The hairclipper's powerful NiMH battery provides up to 75 minutes of cordless power after 8 hour of charging. Giving you maximum power and freedom.

Comfortable grip



The HAIRCLIPPER Series 3000 is designed to be comfortable to use, convenient to handle and easy to operate. The special texture and grip allow you to easily move the clipper and cut all around your head.

Extra adjustable beard comb



Whether you have a beard or want the perfect stubble, just attach the adjustable beard comb and select one of 12 lock-in settings, from 1 to 23mm. There are precisely 2mm between each length. To get a shorter stubble, remove the comb entirely for a close 0.5mm trim.

Easy to clean



Simply click to release the detachable head to quickly release and clean the blades.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Cutting system

Trim-n-Flow technology

Cutter width: 41mm

Cutting element: Stainless steel blades

Number of length settings: 13

Precision (size of steps): By 2mm

Range of length settings: From 0.5 to 23 mm

Accessories

Comb: Adjustable hair comb, Extra adjustable beard comb, Styling comb

Maintenance: Cleaning brush

Ease of use

Cleaning: Removable cutter, Washable blades

Operation: Corded & Cordless use

Maintenance free: No oil needed

Power

Run time: Up to 75 minutes

Charging: 8 hours full charge

Battery type: Ni-MH

Automatic voltage: 100-240 V

Design

Handle: Ergonomic grip & handling

Service

2-year worldwide guarantee

