

# PHILIPS

## Hair clipper

### Hairclipper series 5000

Titanium Blades

24 length settings

90mins cordless use/1h charge

3 beard combs and case



HC5450/83



## HAIRCLIPPER Series 5000 - Cuts twice as fast\* with DualCut technology for a faster, sharper cut

The HAIRCLIPPER Series 5000 is built to last, and engineered to perform. The innovative cutting element, durable titanium blades and adjustable beard and hair combs are designed to give you a fast, sharp cut, time after time.

#### Performance

- Double-sharpened cutting element with reduced friction
- Self-sharpening titanium blades for extra durability
- Turbo power button boosts cutting speed

#### Precise length control

- Easy to select and lock in 24 length settings: 0.5 to 23mm
- Includes 1.5, 3 and 5mm combs for the perfect beard

#### Easy to use

- 90 minutes of cordless use after a 1-hour charge
- 'Quick release' blades for easy cleaning

#### Built to last


- 2yr guarantee plus 3yrs when you register the product online
- Hard case for reliable storage
- The blades never need oiling



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## DualCut Technology



Power through any hair type with our advanced DualCut Technology, which combines a double-sharpened cutting element with low-friction engineering. The innovative cutting element is designed to perform time after time, cutting hair twice as fast as regular Philips clippers, with a robust stainless steel guard for ultimate durability.\*

## Titanium blades



The advanced Titanium blades are harder than steel for ultimate durability. In addition, the blades are self-sharpening to ensure long-lasting performance and accurate cutting, time after time.

## 24 lock-in length settings



Turn the zoom wheel to simply select and lock in the length you want, with 23 length settings from 1 to 23mm, and precisely 1mm between each length. Or you can use it without the comb for a close 0.5mm trim.

## Corded & powerful cordless use



Use the clipper corded or cordless for maximum power and freedom, with 90 minutes of cordless power after 1 hour of charging.

## Turbo boost



The turbo power button boosts cutting speed for a perfect cut even on the thickest hair.

## Easy to clean



Simply click open the detachable head to quickly release and wash the blades.

## 5-year worldwide warranty



All of our grooming products are built to last. They come with a worldwide guarantee and worldwide voltage compatibility. Simply

register your clipper on [www.philips.com/5years](http://www.philips.com/5years) to receive an additional 3 years on top of your standard 2-year Philips guarantee, giving you a 5-year worldwide warranty in total.

## Bonus 1.5, 3 & 5mm beard combs



Use your Philips hair clipper to style your beard. It comes with 3 dedicated beard comb attachments to give you the complete style you want.

## Hard storage case



Your clipper comes with a reliable hard case for complete durability, to ensure it is kept in optimum condition for ultimate power and precision, time after time.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Cutting system

**Cutter width:** 41 mm

**Cutting element:** Titanium blades

**Number of length settings:** 24

**Range of length settings:** From 0.5 to 23 mm

**Precision (size of steps):** By 1 mm

**Precision beard comb:** 1.5mm beard comb,  
3mm beard comb, 5mm comb

## Power system

**Operation:** Corded and cordless

**Charging time:** 1 hour(s)

**Running time:** 90 minutes

**Battery type:** Ni-MH

## Ease of use

**Cleaning:** Washable blades

**Maintenance free:** No oil needed

## Service

**2-year worldwide guarantee:** Yes, Plus 3-  
years with registration

## Storage

**Case:** Hard case

