

PHILIPS

Hair clipper

Hairclipper series 5000

Titanium Blades

24 length settings

90 mins cordless use/1 hr charge

Adjustable beard comb and case



HC5450/93



HAIRCLIPPER Series 5000 - Cuts twice as fast* with DualCut technology for a faster, sharper cut

The HAIRCLIPPER Series 5000 is built to last and engineered to perform. The innovative cutting element, durable titanium blades and adjustable beard and hair combs are designed to give you a fast, sharp cut, time after time.

Easy to use

- 90 minutes of cordless use after a 1-hour charge
- 'Quick release' blades for easy cleaning

Performance

- Double-sharpened cutting element with reduced friction
- Turbo power button boosts cutting speed
- Extra-sharp blades for an extra-sharp result

Built to last


- 2-year guarantee plus 3 years when you register the product online
- Exclusive storage case to store your clipper and accessories
- The blades never need oiling

Precise length control

- Easy to select and lock in 24 length settings: 0.5 to 23mm
- Includes a beard comb for 23 adjustable lengths: 1 to 23 mm

Highlights

DualCut Technology



Power through any hair type with our advanced DualCut Technology, which combines a double-sharpened cutting element with low-friction engineering. The innovative cutting element is designed to perform time after time, cutting hair twice as fast as standard Philips clippers, with a robust stainless steel guard for ultimate durability.*

Titanium blades



Get a perfect yet protective trim with the self-sharpening titanium-coated steel blades, created for long-lasting performance, time after time.

24 lock-in length settings



Turn the zoom wheel to simply select and lock in the length you want, with 23 length settings from 1 to 23 mm and precisely 1 mm between each length. Or you can use it without the comb for a close 0.5 mm trim.

Corded and powerful cordless use



Use the clipper corded or cordless for maximum power and freedom, with 90 minutes of cordless power after 1 hour of charging.

Turbo boost



The turbo power button boosts cutting speed for a perfect cut even on the thickest hair.

Easy to clean



Simply click open the detachable head to quickly release and wash the blades.

5-year worldwide warranty



All of our grooming products are built to last. They come with a worldwide guarantee and worldwide voltage compatibility. Simply


register your clipper at www.philips.com/5years to receive an additional 3 years on top of your standard 2-year Philips guarantee, giving you a 5 year worldwide warranty in total.

Exclusive storage case



The semi-hard storage case securely stores your clipper and all accessories. Keeps all your items together in one place, keeping your bathroom tidy. The new case can easily hold the comb, clipper and adaptor cable.

Bonus adjustable beard comb



Turn the wheel to simply select and lock in the length you want, whether you have a beard or you want perfect stubble. Just attach the adjustable beard comb for 23 lock-in length settings from 1 to 23 mm, with precisely 1mm between each length. Or you can use it without the comb for a close 0.5-mm trim.

No oil needed



No oil needed, for easy maintenance and to save you time.

Specifications

Cutting system

Cutter width: 41 mm

Number of length settings: 24

Precision (size of steps): By 1 mm

Cutting element: Titanium blades

Range of length settings: From 0.5 to 23 mm

Precision beard comb: 1–23 mm adjustable beard comb

Power system

Running time: 90 minutes

Charging time: 1 hour(s)

Battery type: Ni-MH

Operation: Corded and cordless

Ease of use

Maintenance-free: No oil needed

Cleaning: Washable blades

Storage

Case: Exclusive travel case

Service

2-year worldwide guarantee: Yes, Plus 3 years with registration

