

# PHILIPS

Washable hair  
clipper

Hairclipper series  
5000

Trim-n-Flow PRO technology  
28 length settings (0.5-28mm)  
75 min cordless use/8hr charge  
100% washable



HC5612/15



## Fast even haircut

Cut hair flows away for 2x faster\* clipping

Get an even haircut thanks to DualCut and Trim-n-Flow Pro technology. The new comb design prevents hair of any length from getting stuck in the comb, so you can finish your style in one go.

### Performance

- Cut hair flows away for 2x faster\* clipping
- Double-sharpened blades for 2 times faster clipping
- Self-sharpening stainless steel blades

### Easy to use

- Select with the zoom wheel 28 length settings: 0.5 to 28mm
- Up to 75 minutes of cordless use
- Ergonomic handle for more comfort and control
- 100% washable\*\* for easy and fast cleaning
- 2mm click-on comb for stubble

### Built to last

- Zero maintenance saves time and hassle
- 2-year warranty



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## Trim-n-Flow Pro technology



The innovative comb design allows cut hair to flow away from the blades during use, preventing even long hair from getting stuck in the comb, so you can start and finish your style without interruption.

## DualCut Technology



Power through any type of hair with our advanced DualCut technology: an innovative two-sided cutting element that cuts hair twice as fast as one-sided blades.

## 28 lock-in length settings




Turn the zoom wheel to select and lock in the length you want. The 2 adjustable combs cut between 3mm and 28mm, with precisely 1mm between each length. Use the stubble comb of 2mm for short hair cut or to style your beard. Remove the comb entirely for a close 0.5mm trim.

## Corded and cordless use



The hair clipper's powerful battery provides up to 75 minutes of cordless power after 8 hours of charging. Giving you maximum power and freedom.

## 100% washable\*\*



The clipper is waterproof for easy, hassle-free cleaning under the tap. Rinse thoroughly with water only to always keep the clipper working like day one.

## Stainless steel blades



Self-sharpening stainless steel blades are incredibly long-lasting. Even after 5 years, they cut just like they did on day one.

## Comfortable grip



The Hair Clipper Series 5000 is designed to be comfortable to use, convenient to handle and easy to operate. The special texture and grip allow you to easily move the clipper and cut all around your head.

## Zero maintenance



Save time and hassle with long-lasting self-sharpening blades that stay as sharp as day one, even after 5 years. The clipper is 100% washable\*\* for fast and easy cleaning under the tap.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Accessories

**Maintenance:** Cleaning brush

**Comb:** 1 beard comb, 2 hair combs (long and short)

## Cutting system

**Cutter width:** 41 mm

**Number of length settings:** 28

**Precision (size of steps):** By 1 mm

**Cutting element:** Stainless steel blades

**Range of length settings:** From 0.5 to 28 mm

## Ease of use

**Maintenance free:** No oil needed

**Cleaning:** 100% washable\*\*

**Operation:** Corded & Cordless use

## Service

**2-year worldwide guarantee**

## Power

**Battery type:** Ni-MH

