

# PHILIPS

Washable hair  
clipper

Hairclipper series  
5000

Trim-n-Flow PRO technology

28 length settings (0.5–28 mm)

90 min cordless use/1 hr charge

100% washable



HC5630/13



## Fast, even haircut

Cut hair flows away for 2 x faster\* clipping

Get an even haircut thanks to DualCut and Trim-n-Flow Pro technology. The new comb design prevents hair of any length from getting stuck in the comb, so you can finish your style in one go.

### Performance

- Cut hair flows away for 2 x faster\* clipping
- Maximum precision with double blades
- Get a perfect but protective trim
- Extra power when you need it

### Easy to use

- Adjusts to different length settings
- Ergonomic design for comfort and control
- Up to 90 minutes of cordless use
- Hassle-free cleaning
- Click-on comb for stubble
- Easy, organised storage

### Built to last

- The blades never need oiling
- Warranty for purchase protection

# Highlights

## Trim-n-Flow Pro technology



The innovative comb design allows cut hair to flow away from the blades during use, preventing even long hair from getting stuck in the comb, so you can start and finish your style without interruption.

## DualCut Technology



The Philips Hairclipper 3000 features advanced DualCut Technology for maximum precision. It comes with double blades, and is designed to stay as sharp as day 1.

## 28 lock-in length settings



Cut your hair to the exact length you want with 2 adjustable combs that cut between 3 mm and 28 mm at 1 mm increments, a 2 mm stubble comb or remove the comb for a close 0.5 mm trim.

## Cordless and corded use



Don't get tangled up in your cordless hair clippers — one hour charge provides up to 90 minutes of powerful clipping time. Or keep it plugged in for uninterrupted trimming.

## 100% washable\*\*



Simply rinse your clipper under the tap for fast and easy cleaning.

## Turbo mode



The hair clipper for thicker hair. Just press the Turbo mode button for an extra boost of power.

## Comfortable grip



Philips clippers have a textured grip designed for easy handling, so you can cut your hair with control and in comfort.

## Zero maintenance



Clipping power that's easy to maintain—our blades never need oiling.

## 2-year worldwide guarantee



All of our grooming products are built to last. They come with a 2 year warranty, never need to be oiled and are compatible with any voltage worldwide.

## Extra beard comb



Trim your stubble or quickly touch up your hair with the additional 2 mm beard comb.

## Storage pouch



Keep your clipper, combs and accessories in check with the convenient storage pouch.

# Specifications

## Power system

Battery type: Li-Ion

## Accessories

Maintenance: Cleaning brush

Comb: 1 beard comb, 2 hair combs (long and short)

Storage: Soft pouch

## Cutting system

Cutter width: 41 mm

Number of length settings: 28

Precision (size of steps): By 1 mm

Cutting element: Stainless steel blades

Range of length settings: From 0.5 to 28 mm

## Ease of use

Maintenance-free: No oil needed

Cleaning: 100% washable\*\*

Operation: Corded and Cordless use

## Service

2-year worldwide guarantee

