

PHILIPS

Hair clipper

Hairclipper series 9000

Titanium blades

400 length settings

120 mins cordless use/1 h charge



HC9450/13



Digital touch control with Motorised Combs

HAIRCLIPPER Series 9000 gives you total precision and control of your haircut. With Digital Swipe, Motorised Combs, Memory function and a high-performance cutting element, it's the only clipper that consistently delivers the results you expect.

Ultimate precision and control

- Digital Swipe interface
- Easy to select and lock in 400 length settings: 0.5 to 42 mm
- Adjustable hair combs for the best clipping results

Performance

- Self-sharpening titanium blades for extra durability
- Motorised Combs for easy length selection
- Auto Turbo to boost cutting speed
- Double-sharpened cutting element cuts twice as fast*
- 2 year guarantee

Easy to use


- Remembers 3 cutting length settings per comb
- 120 minutes of cordless use after a 1-hour charge



reddot award 2015
winner


Highlights

Digital Swipe interface



The Digital Swipe interface gives you precise feedback on the selected length. Use the touch screen to easily swipe through more than 400 length settings. Quickly browse through lengths or slowly go through each small step of 0.1 mm.

400 lock-in length settings




Use the Digital Swipe to precisely select and lock-in the length you want, with more than 400 length settings from 1 to 42 mm, and precisely 0.1 mm between each length. Or you can use it without the comb for a close 0.5 mm trim.

3 adjustable hair combs



The clipper comes with 3 adjustable hair combs: from 1 to 7 mm, 7 to 24 mm and 24 to 42 mm. Just attach one of the combs for more than 400 lock-in length settings, with 0.1 mm between each length. Or you can use the clipper without the comb for a close 0.5 mm trim.

Titanium blades



The advanced Titanium blades are harder than steel for ultimate durability. In addition, the blades are self-sharpening to ensure long-lasting performance and accurate cutting, time after time.

Motorised Combs



The motor powered length setting system easily selects and locks in the preferred length. The motor powers the comb and allows selecting between lengths with a precision of up to 0.1 mm. This innovative technology gives you the security of clipping all the time at the desired length and achieving consistent results time after time.

Memory Function



This smart clipper remembers your last cutting length and can save 3 others for each comb attachment you put on. Select your preferred length, hold the memory button pressed and the clipper will immediately memorise your setting. You can do this for three different lengths.

Auto Turbo



The Turbo feature automatically boosts the speed when reaching thick hair, ensuring a perfect, effortless cut.



iF DESIGN AWARD 2015

Hair clipper series 9000iF DESIGN AWARD 2015



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



reddot award 2015
winner

Red Dot Award 2015: Winner

Hair clipper series 9000Red Dot Award 2015: Winner

Specifications

Cutting system

Cutter width: 41 mm

Cutting element: Titanium blades

Number of length settings: 400

Precision (size of steps): By 0.1 mm

Range of length settings: From 0.5 to 42 mm

Length selection: Digital Swipe, Motorised

Combs

Accessories

Attachments: 3 hair combs

Ease of use

Cleaning: Removable cutter

Maintenance-free: No oil needed

Memory function

Power system

Motor: Auto Turbo

Battery type: Li-Ion

Operation: Corded and cordless

Running time: 120 minutes

Charging time: 1 hour

Service

2-year worldwide guarantee

