

# PHILIPS

Steam iron with  
non-stick soleplate

Classic

1200 W

Non-stick soleplate

1.7 m cord length



HD1174/49



## Glides 3x easier on your garments\* For faster ironing

This Iconic Philips Classic dry iron comes with non-stick soleplate for good gliding performance on all fabrics. With its redesigned extra-stable heel rest, comfortable handle and slim tip, this quality iron makes ironing fast and easy

### Easy & fast ironing

- Non-stick soleplate for easy and fast gliding on all fabrics
- Slim tip soleplate reaches easily in tricky areas
- Easy temperature control
- Temperature light indicates when the iron is ready

### Comfortable ironing

- Comfortable handle with texturing for easy grip
- Light weight iron for effortless ironing
- CordFix cord winder system for easy cord storage
- Extra-stable heel rest for improved stability

### Long lasting performance

- Tested design for maximum durability
- Long lasting cord for extended lifetime

# Highlights

## Non-stick soleplate

The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.

## Slim tip soleplate




The slim tip of the soleplate allows to reach easily in the most tricky areas, such as between the buttons, when making pleats and in the corners.

## Easy temperature control



The large temperature control dial lets you easily adjust to the right ironing temperature for each kind of fabric, so you can achieve your desired results safely.

## Temperature light-indicator



Temperature light goes on when the iron is heating up and goes off when the soleplate temperature has reached the set level.

## Comfortable handle




The texturing on the handle of the iron ensures a comfortable and ergonomic grip, so that your hand fits well and does not slip during ironing.

## Light weight



The light weight iron combined with the non-stick coating makes ironing greatly easy for fast wrinkle removal.

## CordFix for easy storage



The cord can be wrapped around the heel rest below the CordFix indication, so that the appliance is easy to store.

## Extra-stable heel rest

This iron features a specially designed extra-large heel rest, which gives extra stability when the iron is put in a vertical position.

## Tested design for durability

This design has been tested under rigorous quality measures to provide long-lasting performance.

## Long lasting cord

The quality long-lasting cord ensures long lifetime performance.

# Specifications

## Fast crease removal

Power: 1200 W

## Easy to use

Soleplate name: Non-stick

Power cord length: 1.7 m

## Size and weight

Packaging dimensions (WxHxL):

11.5x12.5x26 cm

Total weight with packaging: 0.77 kg

Weight of iron: 0.65 kg

## Guarantee

2 year worldwide guarantee

## Green efficiency

Product packaging: 100% recycable

User manual: 100% recycled paper

